

Spirax Sarco Product EU REACH SVHC List

In accordance with Article 33(1) of Regulation (EC) No 1907/2006, in the event that an article supplied by Spirax Sarco contains a substance meeting the criteria in Article 57 and identified in accordance with Article 59(1) in a concentration above 0.1 % weight by weight (w/w) by article, Spirax Sarco is required to provide its customers with sufficient information, available to Spirax Sarco, to allow safe use of the article supplied. This information must, as a minimum, include the name of the substance.

The following information is given in accordance with Article 33(1) of Regulation (EC) No. 1907/2006. Spirax Sarco has identified the following products/articles which contain substances of very high concern as listed on the ECHA candidate list, published 19/01/2021.

Product Range	Product	SVHC Name	EC No.	CAS No.
Control Valves	Temperature Control Ancillaries – Adaptors	Lead (Pb)	231-100-4	7439-92-1
	BX and BXRA Gunmetal Self-acting Control Valves	Lead (Pb)	231-100-4	7439-92-1
	Type 58 Temperature Control Valve	Lead (Pb)	231-100-4	7439-92-1
	SB and SBRA Gunmetal Self-acting Temperature Control Valves	Lead (Pb)	231-100-4	7439-92-1
	TW Three-port Self-acting Control Valve For Liquid Systems	Lead (Pb)	231-100-4	7439-92-1
	NS and NSRA Gunmetal Self-acting Control Valves	Lead (Pb)	231-100-4	7439-92-1
	KA31, KA33, KB31, KB33 and KC31 Cast Iron Self-acting Control Valves	Lead (Pb)	231-100-4	7439-92-1
	KX51 and KY51 Bronze Self-acting Control Valves	Lead (Pb)	231-100-4	7439-92-1
	KA51, KB51 and KC51 Bronze Self-Acting Control Valves	Lead (Pb)	231-100-4	7439-92-1
	KX43 and KY43 Steel Self-acting Control Valves	Lead (Pb)	231-100-4	7439-92-1
	KA43, KB43 and KC43 Steel Self-acting Control Valves	Lead (Pb)	231-100-4	7439-92-1
	PF51G Bronze Piston Actuated On / Off Valves	Lead (Pb)	231-100-4	7439-92-1
	DP27T and DP27TE Pilot Operated Pressure/Temperature Control Valves with SG Iron Bodies	Lead (Pb)	231-100-4	7439-92-1
	HL17 High Limit Cut-out	Lead (Pb)	231-100-4	7439-92-1
	DP17T and DP17TE Pilot Operated Pressure/Temperature Control Valves with SG Iron Bodies	Lead (Pb)	231-100-4	7439-92-1
	DP27, DP27E, DP27G, DP27GY, DP27R & DP27Y Pilot Operated Pressure Reducing Valves with SG Iron Bodies	Lead (Pb)	231-100-4	7439-92-1
	37D and 37DE Pilot Operated Temperature Control Valve with SG Iron Body	Lead (Pb)	231-100-4	7439-92-1
Type 130 and HL10 'Safeguard High Limit Control'	Lead (Pb)	231-100-4	7439-92-1	
Pipeline Connectors	PC3 Pipeline Connectors	Lead (Pb)	231-100-4	7439-92-1
	PC4 Pipeline Connectors	Lead (Pb)	231-100-4	7439-92-1
Steam Trap Monitoring Systems	STAPS Wireless Steam Trap Monitoring System	Lead titanium zirconium oxide	235-727-4	12626-81-2
	STAPS Wireless Steam Trap Monitoring System for ATEX and IECEX applications	Lead titanium zirconium oxide	235-727-4	12626-81-2
	STAPS ISA100 Wireless Steam Trap Monitoring System	Lead titanium zirconium oxide	235-727-4	12626-81-2
	STAPS Wireless Head Unit for ISA100.11a applications	Lead titanium zirconium oxide	235-727-4	12626-81-2
Ball Valves	M45i Reduced bore ball valve DN25 to DN150 flanged ASME 150 and ASME 300	Lead (Pb)	231-100-4	7439-92-1
	M10V Ball Valve DN1/4" to 2 1/2"	Lead (Pb)	231-100-4	7439-92-1
	M21Fi ISO Reduced Bore Firesafe API607 Ball Valve DN15 to DN150 Flanged PN40	Lead (Pb)	231-100-4	7439-92-1
	M21Hi ISO Reduced Bore Ball Valve DN15 to DN150 Flanged PN40	Lead (Pb)	231-100-4	7439-92-1
	M21SiJ ISO and M21ViJ ISO Jacketed Reduced Bore Ball Valves DN40 to DN100 Flanged PN40	Lead (Pb)	231-100-4	7439-92-1
	M20S and M20H Ball Valves DN25 to DN150 ANSI Class 150, ANSI Class 300 and PN40	Lead (Pb)	231-100-4	7439-92-1
	M10S Ball Valve DN1/4" to DN2 1/2"	Lead (Pb)	231-100-4	7439-92-1
	M10S Ball Valve DN1/4" to DN2 1/2"	Lead (Pb)	231-100-4	7439-92-1
	M40SiJ ISO and M40ViJ ISO Jacketed Reduced Bore Ball Valves DN40 to DN100 ASME 150	Lead (Pb)	231-100-4	7439-92-1
	M10F ISO Ball Valve DN1/4" to DN2 1/2"	Lead (Pb)	231-100-4	7439-92-1
	M31S ISO Full Bore Ball Valve DN50 to DN200 DIN PN16 (F1 and F4)	Lead (Pb)	231-100-4	7439-92-1

	M31V ISO Full Bore Ball Valve DN50 to DN200 DIN PN16 (F1 and F4)	Lead (Pb)	231-100-4	7439-92-1
	M15 ISO Ball Valve DN1/4" to DN2 1/2"	Lead (Pb)	231-100-4	7439-92-1
	M10HP Ball Valve DN1/4" to DN2"	Lead (Pb)	231-100-4	7439-92-1
	M45 ISO Ball Valve DN25 to DN150	Lead (Pb)	231-100-4	7439-92-1
	M33V ISO Full Bore Ball Valve API 6D DN50 to DN200 ASME (ANSI) 150 and 300	Lead (Pb)	231-100-4	7439-92-1
	M33S ISO Full Bore Ball Valve API 6D DN50 to DN200 Flanged ASME 150 and ASME 300	Lead (Pb)	231-100-4	7439-92-1
	M33F ISO Full Bore Ball Valve API 6D Firesafe API 607 DN50 to DN200 ANSI 150 and ANSI 300	Lead (Pb)	231-100-4	7439-92-1
	M10HTi ISO Tobacco Ball Valve DN1/4" to DN2 1/2"	Lead (Pb)	231-100-4	7439-92-1
	M10Ti ISO Ball Valve DN1/4" to DN2 1/2"	Lead (Pb)	231-100-4	7439-92-1
	M10Pi ISO Ball Valve DN1/4" to DN2 1/2"	Lead (Pb)	231-100-4	7439-92-1
	M10Hi ISO Ball Valve DN1/4" to DN2 1/2"	Lead (Pb)	231-100-4	7439-92-1
	M10HPi ISO Ball Valve DN1/4" to DN2"	Lead (Pb)	231-100-4	7439-92-1
	M21Si ISO and M21Vi ISO Ball Valves DN15 to DN150	Lead (Pb)	231-100-4	7439-92-1
	M40Si ISO and M40Vi ISO Reduced Bore Ball Valves DN25 to DN200 ASME 150 and ASME 300	Lead (Pb)	231-100-4	7439-92-1
	M21HTi ISO (Tobacco) Reduced Bore Ball Valve DN15 to DN150 Flanged PN40	Lead (Pb)	231-100-4	7439-92-1
	M40Hi ISO Reduced Bore Ball Valve DN25 to DN150 Flanged ASME 150 and ASME 300	Lead (Pb)	231-100-4	7439-92-1
	M40HTi ISO (Tobacco) Reduced Bore Ball Valve DN25 to DN150 Flanged ASME 150 and ASME 300	Lead (Pb)	231-100-4	7439-92-1
	M33HT ISO Ball Valve for the Tobacco Industry DN50 to DN200 ASME 150 and ASME 300	Lead (Pb)	231-100-4	7439-92-1
	M33T ISO Full Bore Ball Valve for the Tobacco Industry DN50 to DN200 ASME 150 and ASME 300	Lead (Pb)	231-100-4	7439-92-1
	M33H ISO Full Bore Ball Valve DN50 to DN200 ASME 150 and ASME 300	Lead (Pb)	231-100-4	7439-92-1
	M21Ti ISO Reduced Bore Ball Valve for the Tobacco Industry DN15 to DN150 Flanged PN40	Lead (Pb)	231-100-4	7439-92-1
	M40Ti ISO Reduced Bore Ball Valve for the Tobacco Industry DN25 to DN150 Flanged ASME 150 and ASME 300	Lead (Pb)	231-100-4	7439-92-1
	M140Fa Ball Valve DN1/4" to DN2 1/2"	Lead (Pb)	231-100-4	7439-92-1
	M40Fi ISO Reduced Bore Firesafe API 607 Ball Valve DN25 to DN200 Flanged ASME 150 and ASME 300	Lead (Pb)	231-100-4	7439-92-1
Pressure Reducing / Surplussing Valves	LRV2B and LRV2S Gunmetal Pressure Reducing Valves	Lead (Pb)	231-100-4	7439-92-1
	BRV2S5 and BRV2B5 Gunmetal Pressure Reducing Valves	Lead (Pb)	231-100-4	7439-92-1
	BRV2S and BRV2B SG Iron Pressure Reducing Valves	Lead (Pb)	231-100-4	7439-92-1
	DPS17 Combined Pressure Reducing and Surplussing Valve	Lead (Pb)	231-100-4	7439-92-1
	SRV2S Stainless Steel Pressure Reducing Valve	Lead (Pb)	231-100-4	7439-92-1
	DRV7 and DRV7G SG Iron Pressure Reducing Valves	Lead (Pb)	231-100-4	7439-92-1
	DEP7 SG Iron Excess Pressure Valve	Lead (Pb)	231-100-4	7439-92-1
	DEP7 SG Iron Excess Pressure Valve Materials of Construction	Lead (Pb)	231-100-4	7439-92-1
	DPP17E and DPP17EE Pilot Operated Pressure Reducing Valves with SG Iron Bodies	Lead (Pb)	231-100-4	7439-92-1
Safety Valves	BRV71 and BRV73 SG Iron Pressure Reducing Valves	Lead (Pb)	231-100-4	7439-92-1
	SV405, SV405P, SV405X and SV406 Safety Valves	Lead (Pb)	231-100-4	7439-92-1
Flowmetering	SV615 Safety Valve	Lead (Pb)	231-100-4	7439-92-1
	TVA Flowmeter for Saturated and Superheat Steam Service	Lead (Pb)	231-100-4	7439-92-1
Air Vents and Air Eliminators	TFA Flowmeter for Saturated Steam Service	Lead (Pb)	231-100-4	7439-92-1
	AV13 Air Vent for Steam Systems	Lead (Pb)	231-100-4	7439-92-1
	AE30, AE30A, AE30B and AE30C Automatic Air Eliminators / Air and Gas Vents for Liquid Systems	Lead (Pb)	231-100-4	7439-92-1
	AE30LV Automatic Air Eliminator / Air and Gas Vent for Liquid Systems	Lead (Pb)	231-100-4	7439-92-1
	BPT13 Brass Balanced Pressure Thermostatic Steam Trap	Lead (Pb)	231-100-4	7439-92-1
Strainers and Filters	AE14 SG Iron Automatic Air Vents for Liquid Systems	Lead (Pb)	231-100-4	7439-92-1
	Fig 3 Bronze Strainer	Lead (Pb)	231-100-4	7439-92-1
	Fig 4 Brass Strainer	Lead (Pb)	231-100-4	7439-92-1
Sight Glasses	Fig 12 Brass and Bronze Strainers	Lead (Pb)	231-100-4	7439-92-1
	Sight Check (combined sight glass and check valve)	Lead (Pb)	231-100-4	7439-92-1
	SG13 Brass Sight Glass	Lead (Pb)	231-100-4	7439-92-1
Hosedown Stations	Single Window and Double Window Sight Glasses	Lead (Pb)	231-100-4	7439-92-1
	Hosedown Gun, Hose and Hose Rack	Lead (Pb)	231-100-4	7439-92-1
	TCO1 Temperature Cut-out Valve	Lead (Pb)	231-100-4	7439-92-1
Steam Traps	Thermocirc Steam / Water Mixing Valve	Lead (Pb)	231-100-4	7439-92-1
	BPT13T and BPT13TGX Thermostatic Steam Traps	Lead (Pb)	231-100-4	7439-92-1
	TD3-3 Thermodynamic Steam Traps	Lead (Pb)	231-100-4	7439-92-1
	No.8 Fixed Temperature Liquid Expansion Steam Trap	Lead (Pb)	231-100-4	7439-92-1

Level Controls	WG2 Water Level Gauge	Lead (Pb)	231-100-4	7439-92-1
	SPV1 and SPV3 Sequencing Purge Valves	Lead (Pb)	231-100-4	7439-92-1
Check Valves	LCV 1 Bronze Lift Check Valve	Lead (Pb)	231-100-4	7439-92-1
Vacuum Breakers	VB14 and VB21 Vacuum Breakers	Lead (Pb)	231-100-4	7439-92-1
Condensate Pumps	PPC & PPF Pressure Powered Pumps	Lead (Pb)	231-100-4	7439-92-1
Isolation Valves	HV3 Stop Valve	Lead (Pb)	231-100-4	7439-92-1
Compressed Air Ancillaries	Dri-Line Mk3 Monnier Compressed Air Drain Trap	Lead (Pb)	231-100-4	7439-92-1

Spirax Sarco believes that the information it provides above is accurate. The provided information is based upon data obtained from ongoing due diligence concerning goods and materials provided by third party suppliers. Spirax Sarco provides such information "AS IS", without any express or implied warranty of any kind. Spirax Sarco reserves the right to update and modify this communication, as it believes necessary or appropriate.

Should you have any further questions relating to REACH and the SVHC content of Spirax Sarco products please contact your local sales team, details of which may be found on the Spirax Sarco website <https://www.spiraxsarco.com/>.

Last Updated: 01/07/2021.