





FT14, FT14HC, FTGS14, FTGS14HC 볼후로트식 스팀트랩 용량표 (낮은 차압 조건)

1/2", 3/4", 1" FT14, FTGS14 (DN15, DN20, DN25)



주 : 차압이 1,000 mm H₂O 이상인 경우, TI-S02-28을 참조한다.

1" FT14HC, FTGS14HC (DN25 HC)
1¼", 1½", 2" FT14 (DN40, DN50)



주 : 차압이 1,000 mm H₂O 이상인 경우, TI-S02-28을 참조한다.