

Antal på lager	Varenr.	Beskrivelse		Pris pr. stk. DKK	Kategori	Link til datablad
10	1326295	A3S 1" SW CS	Bellows Sealed Valve	1.199 kr.	AFSPÆRRINGSVENTIL	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/a3s_a3ss-ti-p132-09-en.ashx?rev=b5fd99176f3944b18160b29f1da29d74
8	1326595	A3S 2" SW CS	Bellows Sealed Valve	2.748 kr.	AFSPÆRRINGSVENTIL	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/a3s_a3ss-ti-p132-09-en.ashx?rev=b5fd99176f3944b18160b29f1da29d74
16	393307	BCR3250 24VDC (No Display/Cab)	TDS Controller (Spare)	5.355 kr.	KEDELUDSTYR	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/bcr3250-ti-p693-21-en.ashx?rev=6a3c7237b1e9404c9a6ef64d1a076761
14	4024690	LP20-470 1/2" BSP 470mm	Capacitance Level	4.395 kr.	KEDELUDSTYR	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/im/lp20-im-p402-37-en.ashx?rev=0f5237f938ef4c629e08c43c86b6537b
36	4024560	LP20-550 1/2" BSP 550mm	Capacitance Level Probe	4.801 kr.	KEDELUDSTYR	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/im/lp20-im-p402-37-en.ashx?rev=0f5237f938ef4c629e08c43c86b6537b
4	4024691	LP20-600 1/2" BSP 600mm	Capacitance Level Probe	4.389 kr.	KEDELUDSTYR	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/im/lp20-im-p402-37-en.ashx?rev=0f5237f938ef4c629e08c43c86b6537b
5	4024693	LP20-900 1/2" BSP 900mm	Capacitance Level Probe	4.933 kr.	KEDELUDSTYR	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/im/lp20-im-p402-37-en.ashx?rev=0f5237f938ef4c629e08c43c86b6537b
16	4024669	PA20	Pre-Amplifier Capacitance LP20	2.902 kr.	KEDELUDSTYR	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/im/pa20-im-p402-67-en.ashx?rev=e072e5e41efe41ccb7314148cf1cd82
1	3398720	M10S2 FB DN15 PN40 CS	Ball Valve	1.205 kr.	KUGLEHANE	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/m10si-ti-p133-58-en.ashx?rev=c3adcae79ae3456ea2d50fa5e8e57328
3	3398740	M10S2 FB DN40 PN40 CS	Ball Valve	2.463 kr.	KUGLEHANE	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/m10si-ti-p133-58-en.ashx?rev=c3adcae79ae3456ea2d50fa5e8e57328
1	3398435	M10S4 RB 2" BW Full SS	Ball Valve	3.527 kr.	KUGLEHANE	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/m10si-ti-p133-58-en.ashx?rev=c3adcae79ae3456ea2d50fa5e8e57328
5	3460310	M10Si2 RB 1/2" NPT CS	Ball Valve	514 kr.	KUGLEHANE	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/m10si-ti-p133-58-en.ashx?rev=c3adcae79ae3456ea2d50fa5e8e57328
2	3501015	M33S2 DN100 A150 CS	Ball Valve - 316 Solid Ball	6.770 kr.	KUGLEHANE	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/m33s-ti-p133-63-en.ashx?rev=c86e75dec45e4147a041e5c9ddf946a4
7	175200	AE30C 1/2" BSP BR/EPDM	Air Eliminator Liquid	723 kr.	LUFTUDLADER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/ae30-ti-p017-07-en.ashx?rev=7e3e8e85d9534f928294b66312db030c
1	0781093-0	KA43 DN25 PN40 CS Heating	2-Port Valve	2.579 kr.	SELV VIRKENDE	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/ka_kc-kc-ti-p078-06-en.ashx?rev=f8b59cc25122470bb8d2c0b1c15494bd
2	0239993-0	S6 DN40 PN40 SS	Separator	9.851 kr.	SEPARATOR	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/s6-ti-p023-12-en.ashx?rev=cbb9cd16e18547cfa715a9a476c8d3be
3	12500592	SV615AV 1/2" BSP BZ 2.6-4 Bar	Safety Valve	1.434 kr.	SIKKERHEDSVENTIL	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/im/sv615-im-p316-03-en.ashx?rev=191a0081ef134fca869dd1dbb44d50a1
2	0226000-0	SG2 1.1/2" BSP BR	Sight Glass	715 kr.	SKUEGLAS	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/sg253-ti-p130-01-en.ashx?rev=8cf63040839f4073861a31ddba31edac
1	1637000-0	FIG12SG 1.1/2" BSP SG M100 SS	Strainer	365 kr.	SNAVSSAMLER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/fig_12-ti-p163-01-en.ashx?rev=c718913a8ecb4ebaa892acbb40948610
1	1633361-0	FIG16 3/4" BSP CDT 1/2"	200 Mesh SS Strainer	1.672 kr.	SNAVSSAMLER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/fig_16hp-ti-p169-08-en.ashx?rev=326de6069a534dc88b591a9ff54dad7a
1	1683597-0	FIG34 6" A150 CS 1.6mm SS	Strainer	6.912 kr.	SNAVSSAMLER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/fig_34-ti-p064-01-en.ashx?rev=91759cd27f1b450ea78377b3da5fe32d
6	0810392-0	FIG37 3/4" ANSI150 SG	0.8mm Perf SS Strainer	494 kr.	SNAVSSAMLER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/fig_3716-ti-p081-03-en.ashx?rev=b7859ffbd64d460380917b5f1808734c
1	0814293-0	FIG3716 DN25 PN16 SG 0.8mm SS	Strainer	815 kr.	SNAVSSAMLER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/fig_37-ti-p081-01-en.ashx?rev=15fd3300d24114b0495dfb694c23dc03e
2	51100	BPS32 1/2" BSP STD SS	Balanced Pressure Trap	1.492 kr.	VANDUDLADER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/bps32-ti-p005-03-en.ashx?rev=5fda33360e0a48009ee54a886e1ee589
3	51159	BPS32 1/2" BW SS Std	Balanced Pressure Trap	1.529 kr.	VANDUDLADER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/bps32-ti-p005-03-en.ashx?rev=5fda33360e0a48009ee54a886e1ee589
1	9040187	BT6-BL 1" tube end ASME BPE–	Balanced Pressure Trap	4.584 kr.	VANDUDLADER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/bt6-b-ti-p180-30-en.ashx?rev=e9916197b24d4e8d8f40a3d7892cd611
6	9040186	BT6-BL 3/4" tube end ASME BPE	Balanced Pressure Trap	4.193 kr.	VANDUDLADER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/bt6-b-ti-p180-30-en.ashx?rev=e9916197b24d4e8d8f40a3d7892cd611
1	1803751	BT6-BL DN15 Tri-Clamp ISO1127	SERIES 1 0.6Ra 21.3mm ODx1.6mm	3.670 kr.	VANDUDLADER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/bt6-b-ti-p180-30-en.ashx?rev=e9916197b24d4e8d8f40a3d7892cd611
6	1803851	BT6-BL DN20 Tri-Clamp ISO1127	SERIES 1 0.6Ra 26.9mm ODx1.6mm	4.085 kr.	VANDUDLADER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/bt6-b-ti-p180-30-en.ashx?rev=e9916197b24d4e8d8f40a3d7892cd611
2	1801000	BTS7 1/4" BSP	Balanced Pressure Trap	1.384 kr.	VANDUDLADER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/bts7-ti-p180-03-en.ashx?rev=3e5396368d4245aca33fe02734699478
1	832492	FT43-4.5 2" A125 CI	Ball Float Trap	5.414 kr.	VANDUDLADER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/ft43-ti-s02-21-en.ashx?rev=7fd373dc13c64b0da29e038586c40e63
1	842093	FT43V-14 DN40 PN16 CI	Vertical Ball Float Trap	6.012 kr.	VANDUDLADER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/ft43-ti-s02-21-en.ashx?rev=7fd373dc13c64b0da29e038586c40e63
1	836697	FT44-10C DN40 ANSI300 CS	Ball Float Trap	6.770 kr.	VANDUDLADER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/ft44-ti-s02-14-en.ashx?rev=d40a700c180740d4935f0386892b674b
2	1452060	FTS14X-4.5 1/2" PN25 SS R-L	Ball Float Trap	3.424 kr.	VANDUDLADER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/fts14-ti-p145-01-en.ashx?rev=81d4b9cbbb3c41e19678d5da3f2624ab
2	6140000	ITD32L 1/2" BSP SS SSL1	Thermodynamic Steam Trap	792 kr.	VANDUDLADER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/itd32-ti-p614-01-en.ashx?rev=9174f82dace349c3a57516366d059ecc
1	762860	SMC32Y 1/2" BSP CS	Bimetallic Steam Trap	957 kr.	VANDUDLADER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/smc32-ti-p076-10-en.ashx?rev=36fb3083097a45b594834c8a0c98b442
100	762862	SMC32Y 1/2" SW CS	Bimetallic Steam Trap	1.007 kr.	VANDUDLADER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/smc32-ti-p076-10-en.ashx?rev=36fb3083097a45b594834c8a0c98b442
4	1870954	TDS46M 3/4" A600 SS	Thermodynamic Steam Trap	2.105 kr.	VANDUDLADER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/tds46m-ti-p187-02-en.ashx?rev=5a04cff9481043fdaa80f09a25ba1188
4	1541590	UTD26LY Swivel SS	Thermodynamic Steam Trap + BD	1.345 kr.	VANDUDLADER	https://content.spiraxsarco.com/-/media/spiraxsarco/international/documents/en/ti/utd26-ti-p154-04-en.ashx?rev=951d09d1df4844e0bd8311fe7a6e9469
5	11008161	851sGK-15-f/f-15/25 BSP	EPDM10 Bar Safety Valve	793 kr.	SIKKERHEDSVENTIL	https://www.goetze-group.com/en/products/industry/851-s5716.html

Udvalget opdateres løbende – der tages forbehold for udsolgte varer

Vi henviser til vores generelle betingelser på www.spirax.dk