

spirax sarco

AE30LV

ISO 9001

Automatic Air Eliminator/Air and Gas Vent for Liquid Systems

Description

The AE30LV range of automatic air eliminators/air vents for liquid systems have a lightweight float for use on liquids with a minimum specific gravity of 0.7 and a Viton valve cone for chemical resistance. The body and cap are of a special brass alloy which is dezincification resistant (DZR). It is available as a standard air and gas vent designated AE30LV and with check valve designated AE30LVA.

Standards

This product fully complies with the requirements of the European Pressure Equipment Directive 97/23/EC.


Certification

This product is available with a manufacturer's Typical Test Report. **Note:** All certification/inspection requirements must be stated at the time of order placement.

Sizes and pipe connections

Inlet 1/2" female, outlet 1/4" male both BSP or NPT.

Pressure/temperature limits




The product **should not** be used in this region as damage to the internals may occur.


| Body de | esign conditions | PN10 | | |
|---|-------------------------------|------------------------|--|--|
| PMA | Maximum allowable pressure | 10 bar g @ 120°C | | |
| TMA | Maximum allowable temperature | 120°C @ 10 bar g | | |
| Minimu | m allowable temperature | -10°C | | |
| PMO | Maximum operating pressure | 10 bar g @ 110°C | | |
| TMO | Maximum operating temperature | 110°C at all pressures | | |
| ΔΡΜΧ | Maximum differential pressure | 3 bar g @ 110°C | | |
| Minimum operating temperature 0°C | | | | |
| Designed for a maximum cold hydraulic test pressure of 15 bar g | | | | |
| Minimum specific gravity of liquid 0. | | | | |

Materials

| No. | Part | Material | |
|-----|-----------------------------|-------------------------------------|-----------------|
| 1 | Cap | DZR brass alloy | BS 2872 CZ 132 |
| 2 | Cap 'O' ring | Green Viton 75 | |
| 3 | Body | DZR copper alloy BS 2872 CZ 13 | |
| 4 | Float | Acetal co hostaform/stainless steel | |
| 5 | Valve cone | Syntheyic rubber | Green Viton |
| 6 | Valve seat | Stainless steel | BS 970 431 S29 |
| 7 | Bracket / lever assembly | Stainless steel | BS 1449 304 S11 |
| 8 | Screw | Stainless steel | BS 4183 18/8 |
| 9 | Check valve ball (AE30LVA) | Stainless steel | AISI 440 B |
| 10 | Circlip (AE30LVA) | Stainless steel | BS 970 302 S25 |



Free discharge capacity




If the temperature of the air differs from 16°C, the discharge capacity from the graph can be corrected by miltiplying it by the following equation:

273 + T (T is the actual temperature in °C)

It may be assumed that the temperature of the air is equal to the temperature of the water.

Dimensions/weight (approximate) in mm and kg

| Α | В | С | Weight |
|----|-----|----|--------|
| 56 | 105 | 10 | 0.7 kg |



Safety information, installation and maintenance

For full details see the Installation and Maintenance Instructions (IM-P017-08) supplied with the product.

Installation note:

The automatic air vent should be installed vertically with the inlet at the bottom. We recommend piping the discharge from the air eliminator to a suitable safe place.

How to order

Example: 1 off Spirax Sarco 1/2" AE30LVA automatic air eliminator with check valve screwed BSP.

Spare parts
The spare parts available are shown in solid outline. Parts drawn in broken line are not supplied as spares.


Available spares

Maintenance kit comprising: 2, 4, 5, 9, 10 Valve cone, float, cap 'O' ring, check valve ball and check valve circlip

How to order spares

Always order spares by using the description given in the column headed 'Available spares' and state the size and type of automatic air eliminator/air vent.

Example: 1 - Maintenance kit for a Spirax Sarco ½" AE30LVA automatic air eliminator with check valve.



Recommended tightening torques

| Item | | or mm | * | N m |
|------|------------|----------|----------|---------|
| 1 | 30 | | | 10 - 12 |
| 8 | Cheesehead | | M4 x 6 | |