




## spirax sarco

## Capacity Charts for HM34


## **Inverted Bucket Steam Traps**






For selection see overleaf

## Capacities 3/4" / DN20



For selection see overleaf

Capacities 1" / DN25



**Selection note:** Traps should be selected for the most appropriate working pressure differential and not on the basis of load, For example; DN25 HM34 with a load of 80 kg/h at 7 bar differential should be handled by an HM34/10 and not an HM34/5.