TI-P133-59 CMGT Issue 6

# spirax Sarco M10Si ISO

# Automation Ball Valve DN1/4" to DN21/2"


# **Description**

The M10Si ISO Automation three-piece body ball valve has ISO mounting as standard. It is designed for use as an automated isolating valve, not a control valve, on applications that use steam and other industrial fluids for services ranging from vacuum to the higher temperatures and pressures.

The M10Si ISO Automation ball valve is specifically designed for pneumatic or electric actuation and not manual operation and can be serviced without removing the valve from the pipeline (screwed and welded versions only).

# **ISO** mounting

The integral ISO body mounting allows the valve to be automated without losing seal integrity, as the body does not require disassembly. Manual to remote control may therefore be easily accomplished by the ISO range of Spirax Sarco ball valves.



# Available types

M10Si2 ISO Automation	Zinc plated carbon steel body, PDR 0.8 seats.
M10Si3 ISO Automation	Stainless steel body, PDR 0.8 seats.
M10Si4_ ISO Automation	Complete stainless steel, PDR 0.8 seats.

Note: The nomenclature will be followed with either FB (full bore) or RB (reduced bore).

#### **Standards**

This product fully complies with the requirements of the Pressure Equipment Directive (PED) and carries the **( (** mark when so required.

# Certification

This product is available with certification to EN 10204 3.1.

Note: All certification/inspection requirements must be stated at the time of order placement.

# Sizes and pipe connections

1/4", 3/4", 1/4", 11/4"


# **Options**

- Self-venting ball.
- Extended stems 50 mm (2") and 100 mm (4") to allow full insulation.
- Oval handle for confined spaces. Ideal for trap modules.

# Technical data

Flow characteristic	Modified linear						
Port	Full and reduced bore versions						
Leakage test procedure to ISO 5208 (Rate A)/EN 12266-1 (Rate A)							
Antistatic device	Complies with ISO 7121 and BS 5351						

# Pressure/temperature limits



The product  $\boldsymbol{must}$   $\boldsymbol{not}$  be used in this region.


**A - B** 2" FB and 21/2" RB only

**A - C** 1/4" - 11/2" FB, RB and 2" RB

Note: The flange standard may restrict the maximum operating pressure. Please check with Spirax Sarco.

Body design conditions	PN100
PMA Maximum allowable pressure	100 bar g @ 60 °C
TMA Maximum allowable temperature	260 °C @ 0 bar g
Minimum allowable temperature	-29 °C
PMO Maximum operating pressure for saturated steam service	17.5 bar g
TMO Maximum operating temperature	260 °C @ 0 bar g
Minimum operating temperature	-29 °C
Note: For lower operating temperatures consult Spirax Sarco	
ΔPMX Maximum differential pressure is limited to the PMO	
Designed for a maximum cold hydraulic test pressure of	150 bar g


# **Materials**



Part		Material				
	M10Si2 ISO Automation	Zinc plated carbon steel	ASTM A105			
M10Si2 ISO Au   M10Si3 ISO Au   M10Si4 ISO Au   M10Si4 ISO Au   M10Si4 ISO Au   M10Si4 ISO Au   M10Si3 ISO Au   M10Si4 ISO Au   M10Si3 ISO A	M10Si3 ISO Automation M10Si4 ISO Automation	Stainless steel	ASTM A 182 F 316L			
	M10Si2 ISO Automation	Zinc plated carbon steel	ASTM A105			
Body  Cap  Ball Stem Seat Stem seal  Separator  Belleville washer  Nut  Name-plate - DN (No	M10Si3 ISO Automation M10Si4 ISO Automation	Stainless steel	ASTM A 182 F 316L			
Ball		Stainless steel	AISI 316			
Stem		Stainless steel	AISI 316			
Seat		Carbon/graphite reinforced PTFE	PDR 0.8			
Stem seal		Reinforced PTFE antistatic				
Separator	M10Si2 ISO Automation M10Si3 ISO Automation	Zinc plated carbon steel	SAE 1010			
·	M10Si4 ISO Automation	Stainless steel	AISI 316			
Belleville washer		Stainless steel	AISI 301			
Nut	M10Si2 ISO Automation M10Si3 ISO Automation	Zinc plated carbon steel	SAE 1010			
	M10Si4 ISO Automation	Stainless steel	AISI 304			
Name-plate - DN (Not shown)		Stainless steel	AISI 430			
Stem nut	M10Si2 ISO Automation M10Si3 ISO Automation	Zinc plated carbon steel	SAE 1010			
	M10Si4 ISO Automation	Stainless steel	AISI 304			
	Body  Cap  Ball Stem Seat Stem seal  Separator  Belleville washer  Nut  Name-plate - DN (I	M10Si2 ISO Automation	Body  M10Si2 ISO Automation Stainless steel  M10Si3 ISO Automation M10Si4 ISO Automation M10Si3 ISO Automation			

# Materials continued on next page

# Materials (continued)



No.	Part		Material	
13	Name-plate (I	Not shown)	Stainless steel	AISI 430
15	Bolts	M10Si2 ISO Automation M10Si3 ISO Automation	Zinc plated carbon steel	Grade 5
		M10Si4 ISO Automation	Stainless steel	AISI 304
16	Nuts	M10Si2 ISO Automation M10Si3 ISO Automation	Zinc plated carbon steel	SAE 1010
		M10Si4 ISO Automation	Stainless steel	AISI 304
17	Studs	M10Si4 ISO Automation	Stainless steel	AISI 316
	Note: Item 17	can not be shown as it is only applical	ble to welded versions	
19	Body/cap gas	ket - 'O' ring	EPDM geothermal	
20	Nut locker		Stainless steel	AIS 316
22	Stem seal		PEEK	

# **Dimensions** (approximate) in mm Reduced bore

Size	Α	<b>A</b> 1	A2	А3	D	D1	D2	E
1/4"	56	52	-	-	22	-	-	8
3/8"	56	52	-	-	22	-	-	8
1/2"	63	52	108	130	24	89	95	11
3/4"	68	60	117	150	26	98	105	14
1"	86	84	127	160	31	108	115	21
11/4"	99	94	140	180	37	118	140	25
11/2"	108	102	165	200	41	127	150	31
2"	124	118	178	230	48	152	165	38
21/2"	152	152	-	-	57	-	-	51

# D1, D2 A2, A3 A2, A3

Full bore

Size	Α	<b>A</b> 1	A2	А3	D	D1	D2	E
1/4"	56	58	-	-	22	-	-	8
3/8"	63	60	-	-	24	-	-	11
1/2"	68	64	-	130	26 - 95		14	
3/4"	86	84	-	150	31	-	105	21
1"	99	98	-	160	37	37 - 115		25
11/4"	108	106	-	180	30 41 - 140		31	
11/2"	124	124	-	200	48	-	150	38
2"	152	152	-	230	57	-	165	51

A: Scrd and BW

A1: SW

A2: Flanged ASME 150

A3: Flanged PN40

D: Scrd, BW, SW

D1: Flanged ASME 150

D2: Flanged PN40

E: All versions

Weights (approximate) in kg

Size		Reduced bore		Full	bore
	Scrd/BW/SW	PN40	ASME 150	Scrd/BW/SW	PN40
1/4"	0.65	-	-	0.65	-
3/8"	0.65	-	-	0.72	-
1/2"	0.72	2.30	1.77	0.95	2.60
3/4"	0.95	3.20	2.35	1.60	3.80
1"	1.60	4.20	3.47	2.05	4.70
11/4"	2.05	5.70	4.47	2.75	6.40
1½"	2.75	6.80	5.96	4.25	8.30
2"	4.25	9.50	9.16	7.50	12.80
21/2"	7.50	-	-	-	-

# K, values

Size	1/4"	3/8"	1/2"	3/4"	1"	11/4"	11/2"	2"	21/2"
Reduced bore	2.5	6.8	6	10	27	49	70	103	168
Full bore	2.5	6.8	17	36	58	89	153	205	_

For conversion:  $C_v(UK) = K_v \times 0.963$  $C_v(US) = K_v \times 1.156$ 

# Operating torque (N m)

Size	1/4"	3/8"	1/2"	3/4"	1"	11/4"	1½"	2"	21/2"
Reduced bore	3.25	3.25	3.25	5.50	13.25	20	50	60	75
Full bore	3.25	3.25	5.50	13.25	20	50	60	75	_

The indicated torque values are for valves frequently operated, that are submitted to a maximum differential pressure of 40 bar.

Valves that are subject to long static periods, may require greater break-out torque.

# Safety information, installation and maintenance

For full details see the Installation and Maintenance Instructions supplied with the product.

# How to order example:

1 off Spirax Sarco 1/2" screwed BSP M10Si2FB ISO Automation ball valve.

# **Spare parts**

The spare parts available are shown in solid outline. Parts drawn in a grey line are not supplied as spares.

#### Available spare

Seat, seals and body gasket set

5, 6, 19, 22

### How to order spares

Always order spares by using the description given in the column headed 'Available spare' and state the size and type of ball valve. **Example:** 1 - Seat, seals and body gasket set for a Spirax Sarco ½" M10Si2FB ISO Automation ball valve.

