



Cert. No. LRQ 0963008

ISO 9001

spirax/sarco

TI-P160-02
ST Issue 10

Fig 36 Austenitic Stainless Steel Strainer

Description

The Fig 36 is an austenitic stainless steel integrally flanged Y-type strainer. The standard stainless steel screen in the DN15 to DN80 size range has 0.8 mm perforations, in the DN100 to DN200 size range it has 1.6 mm perforations. Other perforations, mesh sizes and monel screens are available as options. The strainer cap can be drilled and tapped for blowdown and drain valves if required.

Standards

This product fully complies with the requirements of the European Pressure Equipment Directive 97/23/EC and carries the **CE** mark when so required.

Certification

The product is available with a manufacturers' Typical Test Report as standard and EN 10204 3.1 for body and cap by special request. **Note:** All certification/inspection requirements must be stated at the time of order placement.

Optional extras

Strainer screens


Screen Type	Perforations	Mesh
Stainless steel screens	1.6 mm (DN15 to DN80)	
	3.0 mm (DN15 to DN200)	
	Mesh	40, 100, 200
Monel screens	0.8 mm (DN15 to DN80)	
	1.6 mm (DN100 to DN200)	
	3.0 mm (DN15 to DN200)	
	Mesh	100

Blowdown or drain valve connections.

The cap can be drilled to the following sizes to enable a blowdown or drain valve to be fitted.

Strainer size	Blowdown valve	Drain valve
DN15	1/4"	1/4"
DN20 and DN25	1/2"	1/2"
DN32 and DN40	1"	3/4"
DN50 to DN125	1 1/4"	3/4"
DN150 and DN200	2"	3/4"

Pressure/temperature limits



This product **must not** be used in this region.

- A - B Flanged ANSI 300.
- A - C Flanged EN 1092 PN40.
- A - D Flanged ANSI 150.

Body design conditions	ANSI 300 (PN50)
PMA Maximum allowable pressure	41 bar g @ 38°C
TMA Maximum allowable temperature	450°C @ 21 bar g
Minimum allowable temperature	-29°C
	ANSI 150 16 bar g
PMO Maximum operating pressure	PN40 38 bar g
	ANSI 300 41 bar g
TMO Maximum operating temperature	450°C @ 21 bar g
Minimum operating temperature	-29°C

Note: For lower operating temperatures consult Spirax Sarco. Designed for a maximum cold hydraulic test pressure of 76 bar g

Sizes and pipe connections

DN15, DN20, DN25, DN32, DN40, DN50, DN65, DN80, DN100, DN125, DN150 and DN200

Standard flange:


EN 1092 PN16, PN25 and PN40 (DN15 to DN50)

EN 1092 PN25 and PN40 (DN65 to DN150)

EN 1092 PN40 (DN200)

ANSI Class 150 and ANSI Class 300 (All sizes)

JIS/KS flanges are available on request.



Materials

No.	Part	Size	Material
1	Body		Austenitic stainless steel ASTM A351 CF3M
2	Cap	DN15 - DN50	Austenitic stainless steel ASTM A182F316L
		DN65 - DN200	Austenitic stainless steel ASTM A351 CF3M
3	Cap gasket		Reinforced exfoliated graphite
4	Strainer screen		Austenitic stainless steel ASTM A240 316L
5	Cap bolt		Austenitic stainless steel ISO 3506 A2-70

Local regulations may restrict the use of this product to below the conditions quoted.

In the interests of development and improvement of the product, we reserve the right to change the specification without notice.

© Copyright 2008


Kv values

For conversion: $C_v(\text{UK}) = K_v \times 0.963$ $C_v(\text{US}) = K_v \times 1.156$

Size	DN15	DN20	DN25	DN32	DN40	DN50	DN65	DN80	DN100	DN125	DN150	DN200
Perforations 0.8, 1.6 and 3 mm	5	8	13	22	29	46	72	103	155	237	340	588
Mesh 40 and 100	5	8	13	22	29	46	72	103	155	237	340	588
Mesh 200	4	6	10	17	23	37	58	83	124	186	268	464

Dimensions / weights (approximate) in mm and kg

Size	EN 1092 PN16/25/40 A	ANSI 150 A	ANSI 300 A	B	C	Screening area cm ²	Weight
DN15	130	124	130	70	120	28	2.5
DN20	150	142	149	80	130	46	4.5
DN25	160	156	163	95	162	79	5.0
DN32	180	180	180	130	235	135	10.0
DN40	200	200	208	146	260	161	12.0
DN50	230	230	241	180	320	251	16.5
DN65	290	290	290	200	325	325	23.0
DN80	310	310	310	205	330	360	35.6
DN100	351	351	351	255	405	540	38.5
DN125	400	400	400	315	510	840	76.0
DN150	480	475	480	345	560	1 115	109.0
DN200	600	594	600	440	710	1 905	144.0



Safety information, installation and maintenance

For full details see the Installation and Maintenance Instructions (IM-S60-18) supplied with the product.

Installation note:

The strainer should be installed in the direction of flow, as indicated on the body. On applications involving steam or gases the pocket should be in the horizontal plane. On liquid systems the pocket should point downwards. Suitable isolation valves must be installed to allow for safe maintenance and trap replacement.

Maintenance note:

Maintenance can be completed with the strainer in the pipeline, once the safety procedures have been observed. It is recommended that a new gasket is used whenever maintenance is undertaken.

Warning:

The strainer cap gasket contains a thin stainless steel support ring, which may cause physical injury if it is not handled and disposed of carefully.

Disposal

The product is recyclable. No ecological hazard is anticipated with disposal of this product, providing due care is taken.

How to order

Example: 1 off Spirax Sarco DN32 Fig 36 strainer having a stainless steel screen with 0.8 mm perforations. The connections are to be flanged EN 1092 PN40.

Spare parts

The spare parts available are shown in solid outline. Parts drawn in broken line are not supplied as spares.

Available spares


Strainer screen (state material, size of perforations or mesh and size of strainer) **4**

Cap gasket (3 off) **3**



How to order spares

Always order spares by using the description given in the column headed 'Available spares' and state the size and type of strainer and perforation or mesh required.

Example: 1 off stainless steel strainer screen, having 0.8 mm perforations for a DN50 Spirax Sarco Fig 36 strainer having EN 1092 PN40 connections.



Recommended tightening torques

Item	Size	Qty	 or 	mm	N m
5	DN15 - DN25	4	16 A/F	M10 x 30	22 - 25
	DN32 - DN40	4	19 A/F	M12 x 35	40 - 45
	DN50	8	19 A/F	M12 x 35	40 - 45
	DN65	8	19 A/F	M12 x 45	40 - 45
	DN80	8	19 A/F	M12 x 50	40 - 45
	DN100	8	24 A/F	M16 x 50	100 - 110
	DN125	8	30 A/F	M20 x 60	160 - 170
	DN150	8	30 A/F	M20 x 65	210 - 230
	DN200	8	36 A/F	M20 x 75	210 - 230