




FT14 and FT14HC

SG Iron

Ball Float Steam Traps (1" HC, 1¼", 1½" and 2")



Description

The FT14 and FT14HC are iron bodied ball float steam traps having stainless steel working internals and integral automatic air venting facility. These traps are supplied with horizontal screwed connections only and can be maintained without disturbing the pipework. The flow direction is as indicated on the valve body.

Available types

FT14	Standard 1¼", 1½" and 2"
FT14HC	High capacity (1" only) - As standard the FT14HC is available with flow direction in either left-to-right or right-to-left direction. Please state preference when placing an order.

Note: These ball float steam traps are available with either 4.5, 10 or 14 bar (65, 145, 203 psi) internals (ΔPMX).

Capsule

The BP99/32 capsule which is used in the FT14 and FT14HC ball float steam traps is suitable for use on 150 °C (270 °F) superheat @ 0 bar g (0 psi g) and 50 °C (91 °F) superheat @ 32 bar g (464 psi g).

Optional extras will only be supplied if specified at the point of order

A manually adjustable needle valve (designated 'C' on the nomenclature i.e. **FT14-C**) can be fitted to the trap. This option provides a **steam lock release (SLR)** feature in addition to the standard air vent. For further information please consult Spirax Sarco.

The top of the cover can be drilled and tapped up to ⅜" BSP T Rp (ISO 7-1) or NPT for the purpose of fitting a balance line.

The bottom of the cover can be drilled and tapped ⅜" BSP T Rp (ISO 7-1) or NPT for the purpose of fitting a drain cock.

Standards

This product fully complies with the requirements of the European Pressure Equipment Directive 2014/68/EU.

Certification


This product is available with a manufacturers' Typical Test Report.

Note: All certification/inspection requirements must be stated at the time of order placement.

Sizes and pipe connections


1" (FT14HC only), 1¼", 1½" and 2" screwed BSP T Rp (ISO 7-1) and NPT.

Pressure/temperature limits



Size		1" HC and 1¼"		1½" and 2"
Body design conditions		PN25		PN16
PMA	Maximum allowable pressure	25 bar g @ 100 °C (363 psi g @ 212 °F)		16 bar g @ 100 °C (232 psi g @ 212 °F)
TMA	Maximum allowable temperature	300 °C @ 18 bar g (572 °F @ 261 psi g)		220 °C @ 13.5 bar g (428 °F @ 196 psi g)
Minimum allowable temperature		-10 °C (14 °F)		
PMO	Maximum operating pressure for saturated steam service	21 bar g (305 psi g)		14 bar g (203 psi g)
TMO	Maximum operating temperature	275 °C @ 19 bar g (527 °F @ 276 psi g)		220 °C @ 13.5 bar g (428 °F @ 196 psi g)
Minimum operating temperature Note: For lower temperatures consult Spirax Sarco		0 °C (32 °F)		
ΔPMX	Size	1" HC	1¼"	1½" and 2"
	4.5 bar	FT14HC-4.5	FT14-4.5	FT14-4.5
	10 bar	FT14HC-10	FT14-10	FT14-10
	14 bar	FT14HC-14	FT14-14	FT14-14
Product is safe for use under full vacuum conditions				
Designed for a maximum cold hydraulic test pressure of:		38 bar g (551 psi g)		24 bar g (348 psi g)


Materials



No.	Part		Material	
1	Body	1" and 1 1/4"	SG iron	BS EN 1563 JS 1030
		1 1/2" and 2"	Cast iron	DIN 1691 GG 25
2	Cover bolts	1"	Steel	BS 3692 Gr. 8.8
	Cover bolts and nuts	1 1/4"	Steel	ASTM A193 B7
3	Cover gasket	1 1/2" and 2"	Steel	BS 3692 Gr. 8.8
			Reinforced exfoliated graphite	
4	Cover	1" and 1 1/4"	SG iron	BS EN 1563 JS 1030
		1 1/2" and 2"	Cast iron	DIN 1961 GG 25
5	Valve seat	1" and 1 1/4"	Stainless steel	BS 970 431 S29
	Main valve assembly with erosion deflector	1 1/2" and 2"	Stainless steel	BS 3146 Part 2 ANC 2
	Valve seat gasket	1" and 1 1/4"	Stainless steel	BS 1449 304 S11
6	Main valve assembly gasket	1 1/2" and 2"	Reinforced exfoliated graphite	
	Pivot frame assembly set screws	1" and 1 1/4"	Stainless steel	BS 4183 18/8


Materials are continued on the next page

Materials (continued)



No.	Part	Material			
7	Main valve assembly bolts	Bolts	1 1/2"	Stainless steel	ISO 3506-2: A2-70
		Studs and nuts	2"	Stainless steel	BS 6105 A4-80
8	Ball float and lever			Stainless steel	BS 1449 304 S16
9	Support frame		1" and 1 1/4"	Stainless steel	BS 1449 304 S16
10	Pivot frame		1" and 1 1/4"	Stainless steel	BS 1449 304 S16
11	Pivot pin		1" and 1 1/4"	Stainless steel	
12	Erosion deflector			Stainless steel	BS 970 431 S29
17	Air vent assembly			Stainless steel	
18	Air vent seat gasket			Stainless steel	BS 1449 304 S11
19	SLR assembly			Stainless steel	BS 970 303 S21
20	SLR gasket			Mild steel	BS 1449 CS4
21	SLR seal			Graphite	
26	Inlet plate		1 1/2" and 2" only	Stainless steel	BS 1449 304 S16

Capacities



Additional cold water capacities from the thermostatic air vent under start-up conditions

Capacities shown above are based on condensate at saturation temperature.


Under start-up conditions when the condensate is cold the internal thermostatic air vent will be open and provides additional capacity to the main valve.

The following table gives the minimum additional cold water capacities from the air vent.

ΔP bar (psi)	0.5 (7)	1 (15)	2 (29)	3 (44)	4.5 (65)	7 (102)	10 (145)	14 (203)
	Minimum additional cold water capacity kg/h (lb/h)							
1" HC	580	600	650	670	700	1000	1300	1600
1 1/4, 1 1/2" and 2"	(1279)	(1323)	(1433)	(1477)	(1543)	(2205)	(2866)	(3527)

Dimensions/weights (approximate) in mm (in) and kg (lb)

1½" and 2" shown



Size	A	B	C	D	E	F	G	Weight
1" HC	120 (4.7)	110 (4.3)	80 (3.1)	195 (7.7)	160 (6.3)	220 (8.7)	115 (4.5)	6.8 (15.0)
1¼"								6.9 (15.2)
1½"	270 (10.6)	130 (5.1)	108 (4.2)	248 (9.8)	200 (7.9)	270 (10.6)	115 (4.5)	17.5 (38.5)
2"	300 (11.8)	138 (5.4)	125 (4.9)	250 (9.8)	200 (7.9)	288 (11.3)	140 (5.5)	22.0 (48.5)

Safety information, installation and maintenance

For full details see the Installation and Maintenance Instructions (IM-S02-30) supplied with the product.

Installation note:

The FT14 must be installed with the direction of flow as indicated on the body, and with the float arm in a horizontal plane so that it rises and falls vertically.

Disposal

This product is recyclable. No ecological hazard is anticipated with the disposal of this product providing due care is taken.

How to order

Example: 1 off Spirax Sarco 1" screwed BSP T Rp (ISO 7-1) FT14HC-14 ball float steam trap having an SG iron body and cover, with thermostatic air vent - flow direction left-to-right. The cover is to be suitable for tapping ⅜" for drain/balance pipe connection.

Spare parts

The spare parts available are shown in solid outlines. Parts drawn in a grey line are not supplied as spares.


Available spares

Main valve assembly	with float (1" and 1¼")	5, 6, 7, 8, 9, 10, 11	Note: The erosion deflector on the 1" and 1¼" is pressed into the body during manufacture and is not available as a spare.
	with erosion deflector (1½" and 2")	5, 6, 7, 26	
Ball float (1½" and 2")		8	
Air vent assembly		17, 18	
Manually adjustable needle valve (SLR) and air vent assembly		17, 18, 19, 20, 21	
Complete set of gaskets (packet of 3 sets)		3, 6, 18, 20	

How to order spares



Always order spares by using the description given in the column headed 'Available spares' and state the size and type of trap.

Example: 1 - Air vent assembly for a Spirax Sarco 2" FT14-4.5 ball float steam trap.



Recommended tightening torques are shown on the next page

Recommended tightening torques

Item	Size	 or mm		N m	ft lbf
2	1"	17	M10 x 30	29-33	21 - 24
	1¼"	14*	M10 x 30	29-33	21 - 24
	1½"	19	M12 x 60	60-66	44 - 49
	2"	24	M16 x 70	80-88	59 - 65
5	1" and 1¼"	17	-	40-45	30 - 33
7	1" and 1¼"	-	M5 x 20	10-12	7 - 9
	1½"	10	M6 x 20	10-12	7 - 9
	2"	13	M8 x 20	20-24	15 - 18
17	-	17	-	50-55	37 - 41
19	-	21	-	40-45	30 - 33

*Note: Reduced A/F bolt head required

