



TI-P403-25
EMM Issue 6

MS1 Conductivity Meter

Description

The Spirax Sarco MS1 is a battery powered conductivity meter designed for use with liquids. It is particularly suitable for measuring the conductivity of boiler water, feedwater, or condensate samples in order to estimate the level of Total Dissolved Solids, or TDS.

The instrument is fitted with a permanently wired carbon electrode sensor with integral temperature sensor.

A plug-in extension lead is also provided to allow ac resistance measurements to be made on installed conductivity probes in order to check their condition. Calibration to a master instrument or standard solution is possible using the adjustment screw on the side of the case. The instrument is supplied in a protective wallet.

Principal features:

- Automatic temperature compensation.
- Wide selectable range.
- Automatic switch-off.

Limiting conditions



Maximum recommended sensor operating temperature 45 °C (113 °F).

Specification

Ranges	0 to 1.999 μ S/cm
	0 to 19.99 μ S/cm
	0 to 199.9 μ S/cm
Range indication	Decimal point and LED above selection key
Temperature compensation	Automatic, 2% / °C Reference temperature 25 °C (77 °F)
Resolution	0.1 μ S / cm
Accuracy	\pm 1.5% or \pm 3 digits (whichever is greatest) at 25 °C (77 °F)
Calibration range	\pm 20%. 20 turns (approximately)
On/off	Auto-off timer
Sensor	PVC cell with carbon electrodes
Extension cable	Twin core. 3.5 mm jack plug and crocodile clips
Battery	PP3 or equivalent. A low battery warning indicator is fitted

Dimensions/weight (approximate) in mm (in) and grams (lb)

Instrument	80 x 147 x 39 (3.1 x 5.8 x 1.5)
Sensor	140 x 21 (5.5 x 0.8) diameter
Sensor cable	1000 (39)
Extension cable	1000 (39)
Weight	430 (1) with case



How to order : Example: 1 off Spirax Sarco MS1 conductivity meter.