



TI-P186-08  
CTLS Issue 18

## SRV66

# Sanitary Pressure Reducing Valve

### Description

The SRV66 is an angle pattern self-draining sanitary pressure regulating valve of all 316L type stainless steel construction suitable for use on steam, water and inert industrial gases. It is available with sanitary clamp compatible connections, requires no external pressure sensing line and has clean in place (CIP) and sterilise in place (SIP) capability.

Typical applications include: Clean steam, gas and liquid supplies to bioreactors, centrifuges, freeze dryers, sterilisers, autoclaves, process tanks, humidifiers and culinary equipment.

### Valve tightness

Valve tightness is in accordance with EN 60534-4 (leakage rate III for metal sealing and leakage rate V for soft sealing).

### Standard surface finish

Internal wetted parts - Ra < 3.2 µm (126 µin).

### Available options, supplied on request at extra cost:

<b>Polished version</b>	For food, pharmaceutical and superclean applications with surface roughness: Ra ≤ 0.25, 0.4 or 0.8 µm (9.8, 15.7, or 31.4 µin)
<b>Viton (FEPM)</b>	Elastomer soft seat
<b>Special connections</b>	Aseptic
	ASME BPE clamps
	ASME or JIS flanges
	DIN32676 clamps

**Note:** Other connections/constructions available upon request and media wetted metal parts made of 1.4435 for higher resistance to corrosion

### Certification options


The following are available at an additional cost:

- EN10204 3.1 Documentation Pack
- Approvals for FDA USP Class VI 121°C, silicone free, oil and grease free, ADI free
- Surface roughness certificate for wetted metal surfaces


**Note:** All certification/inspection requirements must be stated at the time of order placement.

### Sizes and connections

DN15, DN20, DN25, DN32, DN40, and DN50 (½", ¾", 1", 1¼", 1½", and 2")



## Pressure/temperature limits



 The product **must not** be used in this region.

 The product should not be used in this region or beyond its operating range as damage to the internals may occur.

Body design conditions	Inlet	PN10
	Outlet	see 'Pressure setting range' below
Maximum design pressure	9.5 bar @ 50 °C	(138 psi g @ 122 °F)
Maximum design temperature	300 °C @ 5.8 bar	(572 °F @ 84 psi g)
Minimum design temperature	-10 °C	(14 °F)
Maximum operating temperature	180 °C	(356 °F)
Maximum operating pressure (inlet)	8 bar g	(116 psi g)
Minimum operating temperature	-10 °C	(14 °F)
Designed for a maximum cold hydraulic test pressure of:	15.2 bar g	(220 psi g)

## Pressure setting range

Size	DN15 - DN50 (½" - 2")		
Inlet/outlet rating	PN10/PN2.5	PN10/PN6	PN10/PN10
Spring range	0.3 - 1.1 bar g (4.4 - 16.0 psi g)	0.8 - 2.5 bar g (11.6 - 36.3 psi g)	1.0 - 5.0 bar g (14.5 - 72.5 psi g)
Maximum permitted outlet pressure = 1.5 times maximum set pressure			

## Kv values

To maximise the control accuracy (especially for large load variations) use the Kv values given at 20% offset. For safety valve sizing use the maximum Kv values.

Valve size	DN15	DN20	DN25	DN32	DN40	DN50
Kv at 20% offset	1.6	2.4	3.2	4	4.8	5.6
Maximum Kv	2*	3*	4*	5	6	7

0.9\* alternatively

For conversions:

CV (UK) = KV x 0.963

CV (US) = KV x 1.156

## Sizing

The required  $K_v$  can be calculated from the following formulae:

where:

$\dot{m}_s$  = Steam mass flow (kg/h)

$\dot{V}$  = Liquid volume flow (m<sup>3</sup>/h)

$\dot{V}_g$  = Gas flow at standard conditions: 0 °C @ 1.013 bar a (m<sup>3</sup>/h)

$P_1$  = Upstream pressure (bar absolute)

$P_2$  = Downstream pressure (bar absolute)

$\chi$  =  $\frac{P_1 - P_2}{P_1}$  (pressure drop factor)

$S$  = Specific gravity

$T$  = Absolute average gas temperature (Kelvin = °C + 273)

	Critical pressure drop: $P_2 \leq 0.58 P_1$
	$K_v = \frac{\dot{m}_s}{12 P_1}$
<b>Steam</b>	Non-critical pressure drop: $P_2 \geq 0.58 P_1$
	$K_v = \frac{\dot{m}_s}{12 P_1 \sqrt{1 - 5.67 (0.42 - \chi)^2}}$
<b>Gas</b>	$K_v = \frac{\dot{V}_g}{287} \sqrt{\frac{ST}{(P_1 - P_2)(P_1 + P_2)}}$
<b>Liquid</b>	$K_v = \dot{V} \sqrt{\frac{S}{P_1 - P_2}}$


### Calculating the $K_v$ and selecting a suitable valve

Using your maximum flowrate and smallest differential pressure ( $P_1 - P_2$ ), calculate the required  $K_v$  from one of the above formulae. Select a valve  $K_v$  that is 30% greater than the calculated  $K_v$ . The optimum working range of the selected valve should ideally be within the range of 10 to 70% of its  $K_v$  value.

### Recommended fluid velocities

<b>Steam</b>	Saturated	10 to 40 m/s (32.8 to 131.2 ft/s)
	Superheated	15 to 60 m/s (49.2 to 196.9 ft/s)
<b>Gas</b>	up to 2 bar g (29 psi g)	2 to 10 m/s (6.6 to 32.8 ft/s)
	above 2 bar g (29 psi g)	5 to 40 m/s (16.4 to 131.2 ft/s)
<b>Liquids</b>		1 to 5 m/s (3.28 to 16.4 ft/s)

## Materials



No.	Part	Material	
1 *	Body (integral seat)	Stainless steel	1.4404 (316L)
2 *	Main valve	Stainless steel	1.4404 (316L)
3	Spring housing	Stainless steel	1.4404 (316L)
4	Adjustment screw	Stainless steel	BS 6105 A4 70
5	Spring	Stainless steel	1.4301 (304)
6	Spring clip (not listed)	Stainless steel	1.4301 (304)
7	Diaphragm nut	Stainless steel	BS 6105 A4 70
8 *	Diaphragm plate	Stainless steel	1.4404 (316L)
9	'V' band clamp	Stainless steel	1.4404 (316L)
10	Diaphragm	FPM (Viton)/ PTFE	
11	'O' ring	PTFE	
12	'V' band clamp screw	Stainless steel	BS 6105 A4 70


\* **Note:** Material can be optionally ordered with 1.4435 on No. 1, 2 and 8.

## Dimensions (approximate) in mm

Setting bar range	Size	Nominal diameter DN					
		15	20	25	32	40	50
0.8 - 2.5 1 - 5	AE1*	90	90	90	120	120	120
	AE2*	90/100/110 **		90	120	120	120
	C	200	200	200	200	200	200
	D	138	138	138	138	138	138
0.3 - 11	AE1*	120	120	120	120	120	120
	AE2*	120/140 **			120	120	120
	C	200	200	200	200	200	200
	D	200	200	200	200	200	200

\* Overall length tolerances in accordance with DIN EN 558

\*\* Dimensions can vary according to type of connection, please enquire



## Safety information, installation and maintenance

For full details see the Installation and Maintenance Instructions (IM-P186-09) supplied with the product.

### Installation note:

The SRV66 should always be fitted with the inlet vertical and the spring housing directly above the valve.



### Warning

The pressure reducing valve should not be insulated as this may lead to over heating and destroy the elastomer seals.

## How to order example

1 off Spirax Sarco DN25 SRV66 direct acting sanitary pressure reducing valve having a pressure range of 1 – 5 bar g a PN10/PN6 rating, FPM diaphragm and sanitary clamp compatible connections according to ASME BPE.

## Spare parts

The spare parts available are detailed below. No other parts are supplied as spares.

### Available spares

Maintenance kit consisting of diaphragm and 'O' ring

10, 11

## How to order spares

Always order spares by using the description given in the column headed 'Available spares' and state the size, model and pressure range.

### Example:

1 - Diaphragm and 'O' ring for a Spirax Sarco DN25 SRV66 direct acting pressure reducing valve having a pressure range of 1 - 5 bar, a PN10/PN6 rating and an FPM diaphragm.

