TI-P187-02 CMGT Issue 9



# **Stainless Steel** Thermodynamic Steam Trap with Maintainable Seat

#### Description

The TDS46M is a stainless steel, thermodynamic steam trap that has been specifically designed for low capacity applications up to 46 bar g (667 psi g) (where pipe connections permit).

As standard the unit is available with either screwed, socket weld or flanged connections.

#### TDS46M benefits: - Integral strainer.

- Integral air vent.
- Insulation cap.
- Replaceable seat.

#### **Optional extras**


At extra cost a BDV1 integral blowdown valve can be pre-fitted to the strainer cap, please specify at the time of order placement.

This product fully complies with the requirements of the European Pressure Equipment Directive 2014/68/EU.


#### Certification

These products are available with certification to EN 10204 3.1.

Note: All certification/inspection requirements must be specified at the time of order placement.




#### **Materials**



No.	Part	Material	
1	Body	Stainless steel	1.4308/ASTM A351 CF8
2	Тор сар	Stainless steel (ENP coated)	1.4301/ASTM A479 304
3	Insulating cover	Stainless steel	EN 10088-1 1.4301
4	Disc	Hardened steel	1.2379
5	Seat	Hardened steel	1.2379
6	Bimetal ring	Bimetal	
7	Support	Stainless steel	AISI 304
8	Seat gasket	Graphite foil	
9	Strainer screen	Stainless steel	ASTM A478 316L
10	Strainer cap gasket	Stainless steel	AISI 304
11	Strainer cap	Stainless steel (ENP coated)	1.4308/ASTM A351 CF8

### Pressure/temperature limits (ISO 6552) - Screwed, Socket weld and Flanged EN 1092

Screwed Socket weld Flanged: PN40 PN100




The product **must not** be used in this region or beyond the parameter of the PMA or TMA of the relative end connection.

		Body design conditions PN100						
		PMA	Maximum allowable pressure	100 bar g @ 50 °C	1450 psi g @ 122 °F			
		TMA	Maximum allowable temperature	450 °C @ 58.3 bar g	842 °F @ 846 psi g			
		Minim	um allowable temperature	-50 °C	-58 °F			
A D D	PN100	РМО	Maximum operating pressure	46 bar g @ 450 °C	667 psi g @ 842 °F			
A - B - B	Screwed Socket weld	ТМО	Maximum operating temperature	450 °C @ 46 bar g	842 °F @ 667 psi g			
		Minim	um operating temperature	0 °C	32 °F			
		Minim	um operating pressure	1.5 bar g	22 psi g			
		Maximum operating backpressure		80% of upstream pressure				
		Desig	ned for a maximum cold hydraulic pressure of:	150 bar g	2176 psi g			
		Body	design conditions		PN40			
		РМА	Maximum allowable pressure	40 bar g @ 50 °C	580 psi g @ 122 °F			
		TMA	Maximum allowable temperature	450 °C @ 23.3 bar g	842 °F @ 338 psi g			
		Minim	um allowable temperature	-50 °C	-58 °F			
A - C - C	PN40	РМО	Maximum operating pressure for saturated steam service	28.4 bar g @ 233 °C	412 psi g @ 451 °F			
		ТМО	Maximum operating temperature	450 °C @ 23.3 bar g	842 °F @ 338 psi g			
		Minim	um operating temperature	0 °C	32 °F			
		Minim	um operating pressure	1.5 bar g	22 psi g			
		Maxin	num operating backpressure	80% of upstream pressure				
		Desig	ned for a maximum cold hydraulic pressure of:	60 bar g	870 psi g			

#### Pressure/temperature limits (ISO 6552) - Flanged ASME


Flanged: ASME Class 150 ASME Class 300 ASME Class 600




The product **must not** be used in this region or beyond the parameter of the PMA or TMA of the relative end connection.

		Body	design conditions		ASME Class 600
		PMA	Maximum allowable pressure	99.3 bar g @ 38	°C 1440 psi g @ 100 °F
		TMA	Maximum allowable temperature	450 °C @ 54.8 ba	r g 842 °F @ 795 psi g
		Minim	um allowable temperature	-50	°C -58 °F
	ASME 600	РМО	Maximum operating pressure	46 ba	r g 667 psi g
A - B - B		TMO	Maximum operating temperature	450 °C @ 46 ba	r g 842 °F @ 667 psi g
		Minim	um operating temperature	0	°C 32 °F
		Minim	um operating pressure	1.5 ba	r g 22 psi g
		Maxin	num operating backpressure	8	0% of the upstream pressure
		Desig	ned for a maximum cold hydraulic pressure of:	149 ba	r g 2161 psi g
		Body	design conditions		ASME Class 300
	ASME 300	PMA	Maximum allowable pressure	49.6 bar g @ 38	°C 719 psi g @ 100 °F
		TMA	Maximum allowable temperature	450 °C @ 27.4 ba	r g 842 °F @ 397 psi g
		Minim	um allowable temperature	-50	°C -58 °F
A - C - C		PMO	Maximum operating pressure for saturated steam	n service 33 ba	r g 479 psi g
A-C-C		ТМО	Maximum operating temperature	450 °C @ 27.4 ba	r g 842 °F @ 397 psi g
		Minim	um operating temperature	0	°C 32 °F
		Minim	um operating pressure	1.5 ba	r g 22 psi g
		Maxin	num operating backpressure	8	0% of the upstream pressure
		Desig	ned for a maximum cold hydraulic pressure of:	74.4 ba	r g 1079 psi g
		Body	design conditions		ASME Class 150
		РМА	Maximum allowable pressure	19 bar g @ 38	°C 276 psi g @ 100 °F
		TMA	Maximum allowable temperature	450 °C @ 4.6 ba	r g 842 °F @ 67 psi g
		Minim	um allowable temperature	-50	°C -58 °F
A - D - D	ASME	РМО	Maximum operating pressure for saturated steam	n service 14 ba	r g 203 psi g
A-D-D	150	TMO	Maximum operating temperature	450 °C @ 4.6 ba	r g 842 °F @ 67 psi g
		Minim	num operating temperature	0	°C 32 °F
		Minim	num operating pressure	1.5 ba	r g 22 psi g
		Maxin	num operating backpressure	8	0% of the upstream pressure
		Desig	ned for a maximum cold hydraulic pressure of:	28.5 ba	r g 22 psi g

#### Dimensions (approximate) in mm (in)






Size		Α	В					D	E	F
			Screwed Socket weld		Flanged				Withdrawal	Withdrawal
					PN40 ASME 150, 300, 600	PN100			distance	distance
1/2"	DN15	58 (2.28)	78 (3.07)			210		59 (2.32)		
3/4"	DN20	61 (2.40)	95	92 (3.62)	150 (5.91)	(8.27)	61 (2.40)	63 (2.48)	40 (1.57)	30 (1.18)
1"	DN25	65 (2.56)	(3.74)			230 (9.06)		67 (2.64)		

Weights (approximate) in kg (lbs)

	:	Screwed	Socket weld	Flanged					
5	ize			ASME 150	ASME 300	ASME 600	PN40	PN100	
1/2"	DN15	1.38 (3.04)	1.49 (3.28)	2.46 (5.42)	2.96 (6.53)	3.06 (6.75)	3.06 (6.75)	4.36 (9.61)	
3/4"	DN20	1.64 (3.62)	1.64 (3.62)	3.16 (6.97)	4.06 (8.95)	4.26 (9.39)	3.96 (8.73)	6.26 (13.8)	
1"	DN25	1.90 (4.19)	1.90 (4.19)	4.16 (9.17)	5.16 (11.4)	5.46 (12.0)	4.86 (10.7)	8.16 (18.0)	

#### **Capacities**

Differential pressure psi (x 100 = kPa)



#### Safety information, installation and maintenance

For full details see the Installation and Maintenance Instructions (IM-P187-05) supplied with the product.

#### Installation note:

The TDS46M is designed for installation with the disc in a horizontal plane with the insulating cover at the top.

It is recommended that a non-return valve is fitted when discharging condensate into return lines where backpressure is experienced. It is also recommended that a diffuser is fitted when discharging to atmosphere.

For ease and maintenance, consideration should be given to fitting isolation valves upstream and downstream of the steam trap.

#### How to order

**Example:** 1 off Spirax Sarco DN15 TDS46M thermodynamic steam trap having flanged EN 1092 PN40 connections.

#### **Spare parts**

Please note that the spares shown are the same for the screwed, socket weld and flanged versions.

The spare parts available are shown in solid outline. Parts drawn in a grey line are not supplied as spares.

#### Available spares

Insulating cover	3
Top cap, seat and disc assembly	2, 4, 5, 6, 7, 8
Strainer screen and gasket	9, 10
Set of gaskets (packet of 3 sets)	8, 10
BDV1 blowdown valve retrofit kit	

#### How to order spares


Always order spares by using the description given in the column headed 'Available spares' and state the size and type of trap.

**Example**: 1 off Top cap, seat and disc assembly for a Spirax Sarco DN15 TDS46M thermodynamic steam trap.

## Cautionary note regarding disassembly and assembly of the unit:

Removal of the following parts:

- top cap (2),
- strainer cap (11) and the
- optional BDV2 retrofit kit should be carried out in a workshop, not whilst the trap is connected to the pipeline (PC) connector.



# Recommended tightening torques (for suitably lubricated threads)

Item	Part	mm	N m	(lbf ft)	
2	Тор сар	50 A/F	400	295	
11	Strainer cap	24 A/F	110	46.5 - 48.7	