



Single Window and Double Window Sight Glasses

Description

A range of single and double window sight glasses available in either brass or bronze depending on size with screwed connections.

Standards

This product fully complies with the requirements of the EU Pressure Equipment Directive/UK Pressure Equipment (Safety) Regulations.

Certification


These products are available with certification to EN 10204 2.2.

Note: All certification/inspection requirements must be stated at the time of order placement.

Sizes and pipe connections


Single window $\frac{1}{2}$ ", $\frac{3}{4}$ " and 1" screwed BSP or NPT.

Double window $\frac{1}{2}$ ", $\frac{3}{4}$ ", 1", $1\frac{1}{4}$ ", $1\frac{1}{2}$ " and 2" screwed BSP or NPT.




Material

Single window




Double window



No.	Part	Material	
1	Body	$\frac{1}{2}$ " to 1"	Brass
		$\frac{1}{4}$ " to 2"	Bronze
2	Bezel	Brass	EN 12165 CW617N
3	Window	Toughened soda lime glass	BS 3463
4	Top gasket	Reinforced exfoliated graphite	
5	Bottom gasket	Reinforced exfoliated graphite	

Pressure/temperature limits




The product **must not** be used in this region.

Body design conditions			PN5
PMA	Maximum allowable pressure @ 90 °C (194 °F)	5 bar g	72.5 psi g
TMA	Maximum allowable temperature @ 3.5 bar g (50.8 psi g)	148 °C	298 °F
Minimum allowable temperature		-29 °C	-20.2 °F
PMO	Maximum operating pressure for saturated steam service	3.5 bar g	50.8 psi g
TMO	Maximum operating temperature	148 °C	298 °F
Minimum operating temperature.		0 °C	32 °F
Note: For lower temperatures consult Spirax Sarco.			
Designed for a maximum cold hydraulic test pressure of:		7 bar g	102 psi g
PTMX	Maximum test pressure (steam service)	3.5 bar g	50.8 psi g


Dimensions/weights (approximate) in mm (inches) and kg (lbs)

Single window



Size	A	B	C	D	E	F	Weight
1/2"	89 (3.50)	16 (0.63)	32 (1.26)	64 (2.52)	50 (1.97)	4.8 (0.19)	0.6 (1.32)
3/4"		19 (0.75)	35 (1.38)				0.7 (1.54)
1"		24 (0.94)	38 (1.50)				0.9 (1.98)

Double window



Size	A	B	C	D	E	F	Weight
½"	89 (3.50)		32 (1.26)	64 (2.52)	50 (1.97)	4.8 (0.19)	0.9 (1.98)
¾"			35 (1.38)				1.2 (2.65)
1"							1.9 (4.19)
1¼"	108 (4.25)		51 (2.01)	73 (2.87)			1.8 (3.97)
1½"							2.5 (5.51)
2"							57 (2.24)

Safety information, installation and maintenance

For full details see the Installation and Maintenance Instructions (IM-S32-04) supplied with the product.

Warning:

Under certain conditions corrosive elements in condensate can affect the inside face of the window(s), particularly where caustic alkali and hydrofluoric acid are present. It is recommended that the sight glass is periodically checked for thinning of the window(s). If there is evidence of thinning or erosion damage then the window(s) should be replaced immediately. Always wear eye protection when viewing the contents of the sight glass.

Installation and maintenance note:

Sight glasses should have stop valves fitted on both the inlet and outlet. It is imperative that the upstream stop valve is closed first in order to prevent overpressurisation.
Sight glasses can be fitted in either a horizontal or vertical line on the outlet side of a steam trap. Where the trap is a blast discharge type e.g. thermodynamic, the sight glass must be fitted at least 1 m (3.28 ft) from the trap. This is to ensure that the glass is not subjected to thermal shock or pressure. Reasonable steps should be taken to protect personnel from injury in the unlikely event that the glass breaks.
Ensure access is available for maintenance purposes.

Disposal

The product is recyclable. No ecological hazard is anticipated with disposal of this product providing due care is taken.

How to order

Example: 1 off Spirax Sarco 1" BSP double window sight glass with brass body and removable toughened soda lime glass.

Spare parts

The spare parts available are shown in heavy outline. Parts drawn in a grey line are not supplied as spares.

Available spares


Set of windows and gaskets	3, 4, 5	Set of gaskets	4, 5
----------------------------	---------	----------------	------

How to order spares


Always order spares by using the description given in the column headed 'Available spares' and state the size and type of sight glass.

Example: 1 off Set of windows and gaskets for a 1" Spirax Sarco double window sight glass.



Single window



Double window



Recommended tightening torques

Item	Part	 or 	N m	ft lbf
2	Bezel		60 - 65	44 - 48