

spirax sarco

BRV2S SG Iron Pressure Reducing Valves

Description

The **BRV2S** is a direct acting pressure reducing valves designed for applications using steam or gases such as compressed air. This pressure reducing valve has an SG iron body and is available with screwed connections.

Available types

SG iron body - BRV2S stainless steel bellows

Note: For other types, please contact Spirax Sarco

BRV2S pressure reducing valves are supplied with one of three colour coded springs which are identified by the disc (**18**) located on the adjustment handwheel; **Note:** Where control spring ranges overlap always use the lower range to give better control:

Grey For downstream pressure control: 0.14 to 1.7 bar g

Green For downstream pressure control: 1.40 to 4.0 bar g

Orange For downstream pressure control: 3.50 to 8.6 bar g


Certification

This product is available with a manufacturers' Typical Test Report. **Note:** All certification/inspection requirements must be stated at the time of order placement.

Sizes and pipe connections


½", ¾" and 1" screwed BSP (BS 21 Rp) or NPT.

Pressure/temperature limits



The product **must not** be used in this region.

Body design conditions	PN25
Maximum design pressure	25 bar g @ 210°C
Maximum design temperature	210°C @ 19 bar g
Minimum allowable temperature	-10°C
Maximum operating pressure for saturated steam service	19 bar g @ 210°C
Maximum operating temperature	210°C @ 19 bar g
Minimum operating temperature	0°C
Note: For lower operating temperatures consult Spirax Sarco	
Maximum downstream reduced pressure	8.6 bar g
Maximum differential pressure	19 bar
Maximum recommended turndown ratio	10:1 at maximum flow
Designed for a maximum cold hydraulic test pressure of 38 bar g	
Note: With internals fitted, test pressure must not exceed 19 bar g	



Materials

No. Part	Materials	
1 Spring housing	Aluminium epoxy coated	LM 24
2 Adjustment handwheel	Polypropylene	
3 Top spring plate	Cast iron	DIN 1691 GG 20
4 Pressure adjustment spring	Silicon chrome spring steel	BS 2803 685 A55 Range 2
5 Bellows assembly	Stainless steel	316Ti/316L
	Phosphor bronze/brass	BS 2872 Cz 122
6 Bellows assembly gasket	Stainless steel reinforced exfoliated graphite	
7 Hex. bolt (M8 x 25 mm)	Steel zinc plated	BS 3692 Gr. 8.8
8 Body	SG iron	DIN 1693 GGG 40.3
10 Pushrod	Stainless steel	ASTM A276 316L
11 Valve seat	Stainless steel	BS 970 431 S29
12 Valve seat gasket	Stainless steel	BS 1449 316 S11
13 Valve	Stainless steel	AISI 420
14 Valve return spring	Stainless steel	BS 20056 316 S42
15 Strainer screen	Stainless steel	BS 1449 316 SH
16 Blanking plug	Stainless steel	BS 970 431 S29
17 Compression fitting	Brass	
18 Spring range ID disc	Polypropylene	
19 Bulkhead plate	Stainless steel	316L
20 Tamper-proof pin	Mild steel copper plated	


Note: Items 10, 11, 13, 14, 15 and 19 are all part of one assembly.

Capacities for safety valve sizing

Full lift capacities for safety valve sizing purposes :	Size K _{Vs}	DN15	DN20	DN25
		1.5	2.5	3.0

For conversions: C_V (UK) = K_V x 0.963 C_V (US) = K_V x 1.156

Steam and compressed air capacities



* dm³/s = l/s, 1 l/s \approx 2 c.f.m.

How to use the chart


The curved lines labelled 2, 3, 4, 5 etc., represent upstream pressures. Downstream pressures are read along the vertical line on the left hand side of the chart.

How to use the chart is best described by an example:-

Required, a pressure reducing valve to pass 120 kg/h reducing from 8 to 6 bar. From the downstream pressure of 6 bar on the left hand side of the chart extend out horizontally until the line meets the curved 8 bar upstream line. At this point read vertically downwards where it will be seen that a 1/2" BRV2S will be required.

Dimensions / weights (approximate) in mm and kg

Size	A	B	C	D	Weight
DN15 - 1/2"	83	130	60	25	1.60
DN20 - 3/4"	96	130	60	25	1.70
DN25 - 1"	108	130	60	25	1.95



Safety information, installation and maintenance

For full details see the Installation and Maintenance Instructions (IM-IBR16-13) supplied with the product.

Installation note:

The valve should be installed in a horizontal pipeline with the direction of flow as indicated by the arrow on the valve body.

How to order

Example: 1 off Spirax Sarco DN15 BRV2S pressure reducing valve with SG iron body, stainless steel bellows and fitted with an orange spring for downstream pressure control of 3.5 to 8.6 bar g.

Spare parts

The spare parts available are shown in solid outline. Parts drawn in broken line are not supplied as spares.

Available spares


* Pressure adjustment spring	Grey	0.14 to 1.7 bar g	4, 18
	Green	1.40 to 4.0 bar g	4, 18
	Orange	3.50 to 8.6 bar g	4, 18
* Bellows assembly specify type	Stainless steel	5, 6	
* Spring housing hex. bolts (set of 4)			7
* Valve and seat assembly			6, 11, 12, 19
* Gasket set			6, 12

* Common to all sizes.

How to order spares

Always order spares by using the description given in the column headed 'Available spares' and state the size, type and pressure range of the reducing valve.

Example: 1 off Pressure adjustment spring (orange), having a downstream pressure range of 3.5 to 8.6 bar g for a Spirax Sarco DN15 BRV2S pressure reducing valve.



Recommended tightening torques

Item No.	Part	or mm	N m
7	Hex. bolts	M8 x 25	18 - 24
11	Valve seat	32 A/F	108 - 132