




CSG-FB

Clean steam generation system for Food & Beverage



Description

Spirax Sarco has created a new range of steam generators to deliver food quality steam, specifically for direct injection processes within the food & beverage industry sector, where steam is considered as an ingredient. Primary heating medium is plant steam and the secondary steam should be generated from either de-mineralised or reverse osmosis quality water. All generators are supplied as packaged solutions ready to install and commission.

Product range

Size:	CSG-FB-020 nominal production capacity 200 kg/h (440 lbs/hr)*
	CSG-FB-050 nominal production capacity 500 kg/h (1002 lbs/hr)*
	CSG-FB-110 nominal production capacity 1100 kg/h (2425 lbs/hr)*
	CSG-FB-160 nominal production capacity 1600 kg/h (3527 lbs/hr)*

Versions/Applications: **FB** Food and Beverage steam injection

(*): max steam production at reference operating conditions: primary steam at 10 bar g (145 psi g), production at 5 bar g (73 psi g), feed water at 20 °C (68 °F).

Construction and main features

- System complete, functional and safe
- Compact design
- Modulating pressure and level control: pressure stability and steam quality improvement
- Intelligent PLC with SIMS technology, easy maintenance
- Packaged system with on board wired control panel: easy installation
- Automated start up/commissioning sequence
- EC1935/2004 compliant and in line with FDA requirements as products intended to come into contact with food.
- Configurable options to suit individual needs
- System diagnostics
- Preventive maintenance
- Spirax Sarco's worldwide service.
- Available with a variety of compliances depending upon location including:
 - **CE** mark with EU declaration of conformity according to the following directives
 - 2014/68/EU (PED)
 - 2014/35/EU (LVD)
 - 2014/30/EU (EMC)
 - ASME design with U stamp certification
 - Chinese GB national standard

Design conditions

Primary side	Design pressure	13 bar g	(188 psi g)	For a bespoke design, contact Spirax Sarco	
	Design temperature	195.1 °C	(383 °F)		
Secondary side	Design pressure	8 bar g	(116 psi g)		
	Design temperature	195.1 °C	(383 °F)		
	Safety valve set pressure	7 bar g	(101.5 psi g)		
Feedwater	Design pressure	8 bar g	(116 psi g)		
	Design temperature	without pump	110 °C		(230 °F)
		with pump	100 °C		(212 °F)

Maximum operating conditions

	Without pump	With pump	
Production	Clean saturated steam, up to 6 bar g/165.0 °C (Clean saturated steam, up to 97 psi g/206 °F)		Minimum ambient temperature: 0 °C Designed for indoor installation only, protect from freezing.
Primary side	Plant steam, up to 12 bar g/191.7 °C (Plant steam, up to 174 psi g/345 °F)		
Feedwater	P min. ≥ P clean steam + 0.5 bar g (P min. ≥ P clean steam + 7.2 psi g)	Net positive suction head required (see IM)	
	P max 8 bar g/T max 110 °C (P max 116 psi g/T max 230 °F)	P max 8 bar g/T max 80 °C (P max 116 psi g/T max 176 °F)	

Note: Feedwater is recommended to be demineralised or Reverse Osmosis quality to ensure high performance.

Utilities

	Unit without pump	Unit with pump
Electrical supply (cabinets)	1 x 230 V +N 50/60 Hz 0.4 kW (instr.)	3 x 380 to 500 V +N 50/60 Hz 1 kW (sizes 020-050) (instr.) 1.5 kW (size 110) (instr.) 2 kW (size 160) (instr.)
Air supply (filters)	Minimum 5 bar g (72.5 psi g) to maximum 7 bar g (101.5 psi g) (only for the unit with pneumatic actuators or Integrity test option)	

Performance of the units


Max clean steam production (kg/h), with feedwater at 20 °C:		Clean steam pressure/bar g		
		4.5	4.0	3.5
CSG-FB-020	10.0	225	259	297
	9.5	205	239	276
	9.0	185	219	255
	8.5	164	197	236
	8.0	142	175	212
CSG-FB-050	10.0	588	682	783
	9.5	536	625	732
	9.0	485	571	671
	8.5	431	516	611
	8.0	375	461	553
Plant steam pressure/bar g	10.0	1,302	1,526	1,637
	9.5	1,181	1,395	1,500
	9.0	1,054	1,264	1,500
	8.5	940	1,136	1,360
	8.0	833	1,006	1,223
CSG-FB-110	10.0	1,894	2,220	2,552
	9.5	1,702	2,026	2,371
	9.0	1,511	1,828	2,172
	8.5	1,323	1,629	1,969
	8.0	1,144	1,427	1,760
CSG-FB-160	145.0	496	570	654
	137.8	452	526	609
	130.5	407	482	562
	123.3	361	435	515
	116.0	314	387	467
CSG-FB-020	145.0	1296	1,503	1,747
	137.8	1181	1,379	1,613
	130.5	1069	1,259	1,479
	123.3	951	1,138	1,347
	116.0	826	1,017	1,219
Plant steam pressure/psi g	145.0	2,871	3,363	3,599
	137.8	2,603	3,074	3,307
	130.5	2,324	2,786	3,307
	123.3	2,073	2,503	2,999
	116.0	1,836	2,217	2,695
CSG-FB-050	145.0	4,175	4,894	5,625
	137.8	3,753	4,467	5,228
	130.5	3,331	4,031	4,789
	123.3	2,916	3,581	4,341
	116.0	2,522	3,146	3,880
CSG-FB-110	145.0	4,175	4,894	5,625
	137.8	3,753	4,467	5,228
	130.5	3,331	4,031	4,789
	123.3	2,916	3,581	4,341
	116.0	2,522	3,146	3,880
CSG-FB-160	145.0	4,175	4,894	5,625
	137.8	3,753	4,467	5,228
	130.5	3,331	4,031	4,789
	123.3	2,916	3,581	4,341
	116.0	2,522	3,146	3,880

Dimensions and weights approximate in mm (inches) and kg (lbs) of a standard unit

	Dimensions mm (inches)				Weights kg (lbs)		
	L Length	W Width	H Height	E Clearance for tube bundle extraction	Empty	In operation	Maximum
020	2000 (79)	850 (33)	1840 (72)	1250 (49)	550 (1213)	650 (1433)	(800) (1764)
050	2350 (93)	850 (33)	1840 (72)	1300 (51)	850 (1874)	1050 (2315)	1250 (2756)
110	2450 (96)	1450 (57)	2060 (81)	1600 (63)	1100 (2425)	1450 (3197)	1700 (3748)
160	2950 (116)	1450 (57)	2060 (81)	2000 (78)	1550 (3417)	2050 (4519)	2450 (5401)


Indicated dimensions are the maximum dimensions for a specific configuration of the package.

For detailed dimensions of the unit, size and position of the connections, clearance for the tube bundle extraction, weights and other constructive information, refer to the specific general arrangement drawing of the product.



Connections

	Metric				Imperial			
	020	050	110	160	020	050	110	160
Plant steam inlet connection	DN32 PN25	DN50 PN25	DN80 PN25	DN100 PN25	1½" ANSI 150	2" ANSI 150	3" ANSI 150	4" ANSI 150
Condensate outlet connection	DN25 PN40	DN25 PN40	DN40 PN40	DN40 PN40	1" ANSI 300	1" ANSI 300	1½" ANSI 300	1½" ANSI 300
Clean steam outlet connection	DN50 PN40	DN80 PN40	DN125 PN16	DN150 PN16	2" ANSI 300	3" ANSI 300	5" ANSI 300	6" ANSI 300
Feedwater inlet connection	DN15 PN40	DN20 PN40	DN25 PN40	DN32 PN40	½" ANSI 300	¾" ANSI 300	1" ANSI 300	1¼" ANSI 300
Safety valve discharge	1" G-f	DN50 PN16	DN80 PN16	DN80 PN16	1" NPT	1¼" NPT*	3" NPT	3" NPT
Drain connection	DN25 PN40	DN25 PN40	DN25 PN40	DN25 PN40	1" ANSI 300	¾" ANSI 300	1" ANSI 300	1" ANSI 300
Plant steam condensate drain connection	DN15 PN40	DN15 PN40	DN15 PN40	DN15 PN40	½" ANSI 150	½" ANSI 150	½" ANSI 150	½" ANSI 150
TDS Blowdown connection	DN15 PN40	DN15 PN40	DN15 PN40	DN15 PN40	½" ANSI 150	½" ANSI 150	½" ANSI 150	½" ANSI 150
Sampling system (cooling water in/ out-sample out)	½" BSP- 6 mm	½" BSP- 6 mm	½" BSP- 6 mm	½" BSP- 6 mm	½" BSP	½" BSP	½" BSP	½" BSP
Options								



Product nomenclature and selection guide

The product nomenclature is based on the characteristics of the main elements and options, identified as follows:

Basic configuration	
Design code	E EN
	A ASME
	G GB
	J JBA
Shell type	S Flanged openable-shell and tube, flanged openable without integrated deaerator
Unit size	020 Up to 200 kg/h (440 lbs/hr)
	050 Up to 500 kg/h (1002 lbs/hr)
	110 Up to 1100 kg/h (2425 lbs/hr)
	160 Up to 1600 kg/h (3527 lbs/hr)
(at the reference operating conditions ^)	
Valve actuation type	PN Pneumatic (fail-safe)
	EL Electric (fail-safe)
Control	P1 ABB AC500 series + 7" display
	P2 Allen-Bradley CompactLogix 1700 series + 7" display
	P3 Siemens S7.1200 series + 7" display
Communication interface	C0 None
	C1 BACnet IP
	C2 Profinet
	C3 Modbus TCP/IP
	C4 BACnet MSTP
	C5 Profibus
	C6 Modbus RTU
	C7 BACnet (BTL cert.) IP
C8 BACnet (BTL cert.) MSTP	
Unit frame/Electrical cabinet	0 Base and cabinet made of carbon steel, painted
	1 Open frame and cabinet made of carbon steel, painted
	2 Frame w. side panels and cabinet made of carb. steel, painted
	3 Base and cabinet made of stainless steel (304)
	4 Open frame and cabinet made of stainless steel (304)
	5 Frame with side panels and cabinet made of stainless steel (304)
Control Panel location	S Side
Insulation	1 Steam generator body only
	2 Steam generator and hot piping
	0 Not insulated
Handling wheels and feet	N None (only plates with anchor holes are provided)
	F Adjustable feet
	W Pivoting wheels, lockable, with feet

Product nomenclature and selection guide continued on next page

Product nomenclature and selection guide (continued)

Plant steam inlet shut-off valve	M	Manual stop valve
	AE	Automatic electric isolation valve
Plant steam line trapping	N	None
	T	Plant steam line trapping station
TDS control system	1	Timed TDS blowdown
	2	TDS control with external probe (discontinuous metering)
Sampling cooler	N	None
	S	Sample-cooler and sampling valve
Feedwater pressurisation system	N	None (water P > clean steam P + 0,5 bar g)
	P	Pump with VFD
Independent downstream plant protection	N	None
	T	Temperature limiter
Feedwater pre-heating	N	None
Intelligent diagnostics	N	None
	I1	System diagnostics
	I3	Integrity test
	I4	System diagnostics + Integrity test
Clean steam outlet shut-off valve	N	None
	M	Manual stop valve
	AE	Automatic electric isolation valve
Test and certifications	S	EU PED test and CE marking of the assembly
	U	ASME U stamp
	M	MOM compliance
	K	KGS compliance
	D	DOSH compliance
	GC	GB standard in Chinese language
	GE	GB standard in English language
	SF	None (as assembly)
	U	ASME U stamp in line with FDS requirements.
Level indicator	V	Viscorol (Magnetic Level Indicator)

Product nomenclature example

CSG-FB E S 020-PN P3 C1-1 S 2 F-AE T-2 S P T N I1-AE S V

Not all configurations are available in every country. Please contact your local Spirax Sarco representative for more details.