


---

**DCV10 Stainless Steel Disc Check Valve  
for use with Condensate Pumps  
Installation and Maintenance Instructions**

---



- 1. *Safety information*
- 2. *General product information*
- 3. *Installation*
- 4. *Commissioning*
- 5. *Operation*
- 6. *Maintenance*
- 7. *Spare parts*

---

# 1. Safety information

---

Safe operation of this product can only be guaranteed if it is properly installed, commissioned, used and maintained by qualified personnel (see Section 1.11) in compliance with the operating instructions. General installation and safety instructions for pipeline and plant construction, as well as the proper use of tools and safety equipment must also be complied with.

## 1.1 Intended use

Referring to the Installation and Maintenance Instructions, product markings and Technical Information Sheet, check that the product is suitable for the intended use/application. The product listed below complies with the requirements of the European Pressure Equipment Directive 97/23/EC and carries the CE mark when so required. The product falls within the following Pressure Equipment Directive categories:

	Product		Group 2 Gases	Group 2 Liquids
DCV10	DN25	PN25 rated	SEP	SEP
	DN40	PN25 rated	SEP	SEP
		Class 300 rated	1	SEP
	DN50	PN25 rated	1	SEP
	DN80	PN25 rated	1	SEP

- i) The DCV10 has been specifically designed for use on steam, air or condensate/water which are in Group 2 of the above mentioned Pressure Equipment Directive. The products' use on other fluids may be possible but, if this is contemplated, Spirax Sarco should be contacted to confirm the suitability of the product for the application being considered.
- ii) Check material suitability, pressure and temperature and their maximum and minimum values. If the maximum operating limits of the product are lower than those of the system in which it is being fitted, or if malfunction of the product could result in a dangerous overpressure or overtemperature occurrence, ensure a safety device is included in the system to prevent such over-limit situations.
- iii) Determine the correct installation situation and direction of fluid flow.
- iv) Spirax Sarco products are not intended to withstand external stresses that may be induced by any system to which they are fitted. It is the responsibility of the installer to consider these stresses and take adequate precautions to minimise them.

## 1.2 Access

Ensure safe access and if necessary a safe working platform (suitably guarded) before attempting to work on the product. Arrange suitable lifting gear if required.

## 1.3 Lighting

Ensure adequate lighting, particularly where detailed or intricate work is required.

## 1.4 Hazardous liquids or gases in the pipeline

Consider what is in the pipeline or what may have been in the pipeline at some previous time. Consider: flammable materials, substances hazardous to health, extremes of temperature.

## 1.5 Hazardous environment around the product

Consider: explosion risk areas, lack of oxygen (e.g. tanks, pits), dangerous gases, extremes of temperature, hot surfaces, fire hazard (e.g. during welding), excessive noise, moving machinery.

---

## 1.6 The system

Consider the effect on the complete system of the work proposed. Will any proposed action (e.g. closing isolation valves, electrical isolation) put any other part of the system or any personnel at risk?

Dangers might include isolation of vents or protective devices or the rendering ineffective of controls or alarms. Ensure isolation valves are turned on and off in a gradual way to avoid system shocks.

## 1.7 Pressure systems

Ensure that any pressure is isolated and safely vented to atmospheric pressure. Consider double isolation (double block and bleed) and the locking or labelling of closed valves. Do not assume that the system has depressurised even when the pressure gauge indicates zero.

## 1.8 Temperature

Allow time for temperature to normalise after isolation to avoid the danger of burns. Valves fitted with the Fluoroelastomer (Fluorocarbon polymer FEPM (TFEP)) 'O' ring must not be subjected to temperatures above 315°C (599°F). Above this temperature toxic fumes may be given off. Avoid inhalation of fumes or skin contact.

## 1.9 Tools and consumables

Before starting work ensure that you have suitable tools and/or consumables available. Use only genuine Spirax Sarco replacement parts.

## 1.10 Protective clothing

Consider whether you and/or others in the vicinity require any protective clothing to protect against the hazards of, for example, chemicals, high/low temperature, radiation, noise, falling objects, and dangers to eyes and face.

## 1.11 Permits to work

All work must be carried out or be supervised by a suitably competent person. Installation and operating personnel should be trained in the correct use of the product according to the Installation and Maintenance Instructions.

Where a formal 'permit to work' system is in force it must be complied with. Where there is no such system, it is recommended that a responsible person should know what work is going on and, where necessary, arrange to have an assistant whose primary responsibility is safety.

Post 'warning notices' if necessary.

## 1.12 Handling

Manual handling of large and/or heavy products may present a risk of injury. Lifting, pushing, pulling, carrying or supporting a load by bodily force can cause injury particularly to the back. You are advised to assess the risks taking into account the task, the individual, the load and the working environment and use the appropriate handling method depending on the circumstances of the work being done.

## 1.13 Residual hazards

In normal use the external surface of the product may be very hot. If used at the maximum permitted operating conditions the surface temperature of the product may reach temperatures in excess of 200°C (392°F).

Many products are not self-draining. Take due care when dismantling or removing the product from an installation (refer to 'Maintenance instructions').

---

## 1.14 Freezing

Provision must be made to protect products which are not self-draining against frost damage in environments where they may be exposed to temperatures below freezing point.

## 1.15 Disposal

Unless otherwise stated in the Installation and Maintenance Instructions, this product is recyclable and no ecological hazard is anticipated with its disposal providing due care is taken. However, special care must be taken to avoid potential health hazards associated with decomposition/burning of the fluorocarbon polymer FEPM (TFEP) 'O' ring:

### Fluoroelastomer (Fluorocarbon polymer FEPM (TFEP)):

- Can be landfilled, when in compliance with National and Local regulations.
- Burning is not recommended, unless conducted by an approved / licenced incineration agency.
- Is insoluble in aqueous media.

## 1.16 Returning products

Customers and stockists are reminded that under EC Health, Safety and Environment Law, when returning products to Spirax Sarco they must provide information on any hazards and the precautions to be taken due to contamination residues or mechanical damage which may present a health, safety or environmental risk. This information must be provided in writing including Health and Safety data sheets relating to any substances identified as hazardous or potentially hazardous.

## — 2. General product information —

### 2.1 General description

The DCV10 disc check valve has been designed specifically for use with Spirax Sarco's MFP14 and APT14HC mechanical and automatic pump-traps. The check valve ensures the correct flow of condensate and other suitable fluids through these condensate pumps and also prevents reverse flow.

#### Standards

The DCV10 is designed in accordance with BS EN 14341:2006.

This product fully complies with the requirements of the European Pressure Equipment Directive 97/23/EC.

#### Shut-off

Shut-off conforms to EN 12266-1:2003 Rate F.

#### Certification

This product is available with certification to EN 10204 3.1. **Note:** All certification/inspection requirements must be stated at the time of order placement.

**Note:** For additional product data see Technical Information Sheet TI-P601-32.




Fig. 1 DCV10


### 2.2 Sizes and pipe connections

The PN25 design is available in sizes DN25, DN40, DN50 and DN80 to fit between EN 1092 PN16 and JIS/KS 10K flanges.


**Please note:** The Class 300 design is available in size DN40 only to fit between ASME B 16.5 (ANSI) Class 150 and Class 300 flanges.

## 2.3 Pressure/temperature limits

### PN25



### Class 300



 The product **must not** be used in this region.

**A - B** For fitting between Class 150 and Class 300 flanges.

**A - C** For fitting between EN 1092 PN16 and JIS/KS 10K flanges.

Body design condition		PN25 or Class 300	
PMA	Maximum allowable pressure	PN25	25 bar g @ 0°C (362 psi g @ 32°F)
		Class 300	49.6 bar g @ 0°C (719 psi g @ 32°F)
TMA	Maximum allowable temperature	PN25	200°C @ 17.2 bar g (392°F @ 249 psi g)
		Class 300	200°C @ 34.5 bar g (392°F @ 500 psi g)
Minimum allowable temperature		-10°C (14°F)	
PMO	Maximum operating pressure	PN25	25 bar g @ 0°C (362 psi g @ 32°F)
		Class 300	49.6 bar g @ 0°C (719 psi g @ 32°F)
TMO	Maximum operating temperature	PN25	200°C @ 17.2 bar g (392°F @ 249 psi g)
		Class 300	200°C @ 34.5 bar g (392°F @ 500 psi g)
Temperature limits		-10°C to +200°C (14°F to 392°F)	
Minimum operating temperature		-10°C (14°F)	
Designed for a maximum cold hydraulic test pressure of:	PN25	37.5 bar g	(544 psi g)
	Class 300	74.4 bar g	(1079 psi g)

---

## 3. Installation

---

**Note:** Before actioning any installation observe the 'Safety information' in Section 1.

Referring to the Installation and Maintenance Instructions, product markings and Technical Information Sheet, check that the product is suitable for the intended installation:

- 3.1** Check materials, pressure and temperature and their maximum values. If the maximum operating limit of the product is lower than that of the system in which it is being fitted, ensure that a safety device is included in the system to prevent overpressurisation.
- 3.2** Determine the correct installation situation and the direction of fluid flow.
- 3.3** Disc check valves simply fit between two pipe flanges (see Figure 2). Standard gaskets are used either side of the valve together with longer bolts or studs. Note: Flanges, bolts (or studs), nuts and joint gaskets are to be provided by the installer. Normal sensible flange bolting practice should be followed e.g. torque tightening the bolts in opposite sequence.
- 3.4** The DCV10 must be installed close coupled to the pump. It can be fitted in either a horizontal or vertical line in accordance with the direction of flow arrow on the body.  
**Note:** Flanges, bolts (or studs), nuts and gaskets to be supplied by the installer.




Fig. 2

---

## 4. Commissioning

---

After installation or maintenance ensure that the system is fully functional. Carry out tests on any alarms or protective devices.

## 5. Operation

The DCV10 is opened by the pressure and flow of condensate and is closed by the pressure of the spring when flow ceases and before reverse flow occurs.




Fig. 3

### K<sub>V</sub> values

Size	DN25	DN40	DN50	DN80
K <sub>V</sub>	10.8	26	43	80

For conversion:  $C_V(\text{UK}) = K_V \times 0.963$      $C_V(\text{US}) = K_V \times 1.156$

### Opening pressures in mbar

Differential pressures with zero flow.

→ Flow direction

DN	DN25	DN40	DN50	DN80
↑	25	28	29	31
→	22.5	24.5	24.5	25.5
↓	20	20	20	20

## 6. Maintenance

This product is non-maintainable.

## 7. Spare parts

There are no spare parts available for this product.

### How to order a new product

Example:

1 off Spirax Sarco DN80, DCV10 stainless steel check valve  
to fit between PN16 flanges for use with an MFP14 automatic pump.