



M70i and M80i
SANITARY BALL VALVES
FOR HIGH PURITY
APPLICATIONS

SANITARY BALL VALVE

from Spirax Sarco

ABOUT THE SANITARY BALL VALVE

High purity applications demand the very best in system and product performance, and design. With Spirax Sarco you can be confident of receiving the best possible solution. You can trust us to meet your exact requirements, and to provide the knowledge, service and products that you can depend on.

Spirax Sarco's range of sanitary ball valves form part of a comprehensive product range for high purity applications, where system integrity, product quality and documentation are paramount.

The M70i (½" to 2") and M80i (2½" to 4") are 316L stainless steel ball valves that have been designed in accordance with ASME BPE for the pharmaceutical, bio-processing, food and beverage, and other high purity industries, where bacteria and media deposits can put product quality at risk.

Understanding the importance of documentation within the high purity environment, we ensure material test reports (MTR's) and certificates of compliance are available as standard.

INDUSTRIES AND APPLICATIONS

- Bioprocessing
- Pharmaceutical
- Semi-conductor
- Food and dairy
- Brewing and beverages
- Cosmetics
- Pure steam
- Clean steam
- CIP/SIP
- Clean gases
- High purity water
- Process media



THE RANGE AT A GLANCE

Sanitary ball valve model*	Body material	Valve size	FDA and USP class VI seals	Lockable handle	Surface finish
M70i	Forged 316L	½" to 2" (2½" to 4" available to special order)	As standard	As standard	Standard Mechanically polished to 0.5 micron Ra (20 micro-inch) Optional Electropolished to 0.375 micron Ra (15 micro-inch)
M80i	Investment cast 316L	2½" to 4"	As standard	As standard	Standard Electropolished to 0.375 micron Ra (15 micro-inch)

Actuation note: Spirax Sarco's type BVA200 series pneumatic actuators and LSB type limit switches can be supplied fitted to the M70i and M80i where actuation is required. Contact Spirax Sarco for further details.

SUMMARY OF KEY FEATURES AND BENEFITS

	Key features	Key reasons	Key benefits
	True port design	Internal diameter of valve precisely matches those of the connecting tubing eliminating potential dead spaces.	Facilitates free draining, eliminating areas where media can pool and create a potential for contamination.
	Fully traceable high integrity material	Both the M70i and M80i are manufactured from high quality 316L stainless steel with controlled low ferrite content as standard (<1% M70i and <5% M80i). Material certification supplied as standard.	Ensures system integrity, and reduces risk of producing rouge.
	Designed with orbital welding in mind	Tube weld end tangent lengths in accordance with ASME BPE. Material composition (including sulphur 0.005% to 0.017%) in accordance with ASME BPE.	Enabling automatic orbital welding to be performed without valve disassembly. Helping to give a consistent fully penetrated weld.
	ISO 5211 mounting pads as standard	Allowing simple attachment of actuators, limit switches and extended handles.	International standard allows for simple consistent installation.
	Superior sealing	High temperature Dyneon TFM™ seats and cavity fillers as standard.	Suitable for continuous steam service. Cavity filler eliminates crevice around ball, which can lead to media pooling and bacteria growth.
	Protective packaging	The M70i and M80i are finished, and packed in a segregated clean environment. Each valve is end capped and sealed in a plastic bag, in accordance with ASME BPE.	Guarantees that the product is delivered in top condition with no risk of external contamination.
	Part of a dedicated high purity product range from Spirax Sarco	The M70i and M80i are only part of a comprehensive range of products developed specifically for clean steam and other high purity applications.	Providing customers a single source option for all their clean steam and high purity needs.



Regional Hub Offices

NORTHEAST
 Spirax Sarco, Inc.
 7760 Olentangy River Road
 Suite 120
 Columbus, OH 43235
 Phone: (614) 436-8055
 Fax: (614) 436-8479

MIDWEST
 Spirax Sarco, Inc.
 1500 Eisenhower Lane
 Suite 600
 Lisle, IL 60532
 Phone: (630) 493-4525
 Fax: (630) 724-9176

MID-ATLANTIC
 Spirax Sarco, Inc.
 4647 Saucon Creek Rd.
 Suite 102
 Center Valley, PA 18034
 Phone: (800) 251-7676
 Fax: (800) 996-3232

SOUTHWEST
 Spirax Sarco, Inc.
 203 Georgia Ave.
 Deer Park, TX 77536
 Phone: (281) 478-4002
 Fax: (281) 478-4615

SOUTHEAST
 Spirax Sarco, Inc.
 115 Atrium Way, Suite 118
 Columbia, SC 29223
 Phone: (800) 883-4411
 Fax: (803) 865-0459

WEST
 Spirax Sarco, Inc.
 1930 East Carson Street
 Suite 102
 Long Beach, CA 90810
 Phone: (310) 549-9962
 Fax: (310) 549-7909

SPIRAX SARCO, INC.
 1150 NORTHPOINT BLVD.
 BLYTHEWOOD, SC 29016
 t: 800.883.4411
 or 803.714.2000
 f: 803.714.2222
www.spiraxsarco.com/us

