



Stainless Steel Float and Thermostatic Steam Traps FTS150, FTS300



Description

The trap contains a float valve mechanism which modulates to discharge condensate continuously at steam temperature, while non-condensable gases are released by a separate internal balanced pressure thermostatic air vent.

Typical applications

All process equipment, particularly when controlled by modulating temperature control valves, unit heaters, air heating coils, heat exchangers and steam main drip stations.

Model	FTS150V	FTS300V	FTS150H	FTS300H
PMO	150 psi g	300 psi g	150 psi g	300 psi g
Sizes	½" Vertical		½" Horizontal	
Connections	NPT			
Construction	Stainless Steel Cover, Body and Internals			
Options	Socket Weld to ANSI B16.11			




Limiting operating conditions

PMO	Maximum Operating Pressure	FTS150:	150 psi g (10 bar g)
		FTS300:	300 psi g (21 bar g)
Maximum Operating Temperature of superheat at all operating pressures			572 °F (300 °C)

Pressure shell design conditions


PMA	Maximum allowable pressure	450 psi g/up to 750 °F (31 bar g/up to 400 °C)
TMA	Maximum allowable temperature	750 °F/0-450 psi g (400 °C/0-31 bar g)

Materials



No.	Part	Material	
1	Body	Stainless Steel	AISI 304
2	Cover Screws	Stainless Steel	AISI 304
3	Cover Gasket	Graphite	
4	Cover	Stainless Steel	AISI 304
5	Valve Seat	Stainless Steel	
6	Valve Seat Gasket	Stainless Steel	
7	Float Screw and Washer	Stainless Steel	
8	Ball Float and Lever	Stainless Steel	
9	Air Vent Assembly	Stainless Steel	
10	Valve Seat Bracket	Stainless Steel	
11	Pivot Pin	Stainless Steel	
12	Body Retaining Ring	Stainless Steel	AISI 304

Dimensions/weights (approximate) in inches (mm) and lbs (kg)



Size	A	B	C	Weight
1/2"	5.3 (135)	5.4 (137)	6.1 (155)	6 lb (2.7 kg)

Capacities lb/hr hot condensate

	Inlet pressure																Orifice size
	psi g (bar)	10 (.7)	15 (1.0)	20 (1.4)	25 (1.7)	30 (2.1)	40 (2.8)	50 (3.4)	75 (5.2)	100 (6.9)	125 (8.6)	150 (10.3)	175 (12.1)	200 (13.8)	250 (17.2)	300 (20.7)	
FTS150	300	350	385	420	450	500	540	625	700	760	800	-	-	-	-	.100" (2.54 mm)	
FTS300	145	170	190	200	220	240	260	310	330	370	400	420	440	470	510	.070" (1.78 mm)	

For kg/h multiply by .454

Sample specification

Steam traps shall be of the mechanical ball float type having stainless steel bodies and forged steel covers, NPT connections, and all stainless steel valve heads and seats. Incorporated into the trap body shall be a stainless steel balanced pressure thermostatic air vent capable of withstanding 572 °F (300 °C) temperature and resisting waterhammer without sustaining damage. Internals of the trap shall be completely servicable without disturbing the piping.

Installation

A pipeline strainer should be installed ahead of any steam trap. Full port isolating valves should be placed to permit servicing. The trap should be installed below the drainage point of the equipment with a collecting leg before the trap, in a position so that the float arm is in a horizontal plane and the float rises and falls vertically, with the flow direction as indicated on the cover. Refer to IMI 2.300 for complete instructions.

Maintenance

This product can be maintained without disturbing the piping connections. Complete isolation from both supply and return line is required before any servicing is performed.

The trap should be disassembled periodically for inspection and cleaning of the valve head and seat, operating mechanism and air vent.

Worn or damaged parts should be replaced using a complete valve mechanism assembly and/or air vent assembly. Complete installation and maintenance instructions are given in IMI 2.300, which accompanies the product.

Spare parts

Gasket Kit (3 of each)	B, F
Air Vent Kit	H, J, L, M, N, V
Valve Mechanism Kit	C, D, E, F, G
Float Kit	P

