spirax sarco

Thermodynamic Steam Trap TD42

Thermo-

The Thermodynamic steam trap cycles periodically to discharge condensate very near to steam temperature. It is unaffected by waterhammer or superheat.

	1			
Model	TD42 L	TD42 H		
РМО	600 psig			
Sizes	1/2", 3/4", 1"	1/2", 3/4"		
Connections	NPT			
Construction	Stainless Steel			
Options	Blowdown valve			

Limiting Operating Conditions Max. Operating Pressure (PMO)

Max. Operating Temperature

600 psig (42 barg)

752°F (400°C) at all operating pressures

Minimum pressure for satisfactory operation is 3.5 psi, 0.25 bar. Maximum back pressure should not exceed 80% of the inlet pressure under any conditions of operation, otherwise the trap may not shut.

Pressure Shell Design Conditions

PMA Max. allowable pressure 853 psig/528°F 609 psig/752°F

914 psig/up to 248°F 63 barg/up to 120°C 59 barg/276℃ 42 barg/400°C

400°C/0-42 barg

TMA Max. allowable temperature 752°F/0-609 psig



Typical Applications

Steam main drainage, tracer lines, process equipment, outdoor installations subject to freezing.



001								
No.	Part	Material						
1	Body	Stainless Steel (w/ENP)	ASTM A743 GrCA40F					
2	Cap Assembly	Stainless Steel / Ceramic	AISI 416					
3	Disc	Stainless Steel	AISI 420					
4	Cap Gasket	Stainless Steel						
5	Strainer Screen	Stainless Steel (.031 Perf)	AISI 304					
6	Strainer Cap	Stainless Steel	AISI 416					
7	Blowdown Valve (opt	ional) Stainless Steel						

Local regulation may restrict the use of this product below the conditions quoted. Limiting conditions refer to standard connections only. In the interests of development and improvement of the product, we reserve the right to change the specification.

Thermodynamic Steam Trap TD42

Dimensions (nominal) in inches and millimeters

Size	А	В	С	D	E	Weight Ib/kg	
						TD42L	TD42H
1/2"	2.0 51.5	3.1 78	2.2 55.5	3.7 93	.79 20	1.6 0.78	1.7 0.8
3/4"	2.1 54.5	3.4 84.4	2.4 61.5	4.1 105	.79 20	1.9 0.93	2.2 1
1"	2.3 58	3.8 96	2.5 64.5	4.3 109	.79 20	2.4 1.1	-
with Blo	wdown Val	ve					
1/2"	2.0 51.5	3.1 78	2.8 71	4.3 109	.79 20	2.2 1.0	2.3 1.1
3/4"	2.1 54.5	3.4 84.4	3.1 80	4.8 122	.79 20	2.65 1.2	2.75 1.25
1"	2.3 58	3.8 96	3.3 85	5.1 130	.79 20	3.85 1.75	-

Options

Blowdown Valve – When the blowdown valve is opened, loose material collected by the strainer is blown to atmosphere. Because a wrench is used to open the valve, the operator is clear of the blowdown stream.

Sample Specification

Steam trap shall be stainless steel thermodynamic type, integral seat design with hardened disc and seating surfaces, and oxidation resistant (ENP) finish. Trap to contain inlet Y strainer, and when required, shall be provided with integral blowdown valve and insulating cover.

Installation

The trap will operate in any position, but the preferred installation is in a horizontal pipe. Full-port isolating valves should be installed upstream and downstream of the trap.

Maintenance

This product can be maintained without disturbing the piping connections. Complete isolation of the trap from both supply and return line is required before any servicing is performed.

Although occasional operation of the optional blowdown valve will remove most of the accumulated debris, the trap should be disassembled periodically for cleaning of the strainer screen and inspection and cleaning of the disc and seat.

The only wearing parts of the trap are the disc and seat ring. A worn disc can be replaced, and slight seat ring wear can often be corrected by resurfacing on a lapping plate.

Complete installation and maintenance instructions are given in an IMI Sheet, available upon request.





Available spare parts are shown in heavy line. Parts drawn in broken line are not supplied as spares. Spirax Sarco, Inc. 2017

0

TI-2-502-US 6.17

Telephone: (803) 714-2000 FAX (803) 714-2222