




## M800 Gas Flow Computer



### Description

The M800 gas flow computer receives signals from various pipeline transmitters and converts them to display flowrate, total flow, pressure and temperature. The flow computer operates with Gilflo, ILVA, linear flowmeters, vortex and orifice plates. The M800 can provide density compensation for saturated and superheated steam with suitable inputs from pressure and/or temperature transmitters. Panel and wall mounting versions are available.

Operator settable alarm limits are provided to give a warning when the flowrate, temperature or pressure goes above or below specified limits. These alarms are indicated on a graphic display and can be transmitted via 2 relays (see 'Options' below). A digital pulsed output is provided as standard to signal mass or energy (per pulse).

A 4-20 mA analog output channel is also provided to enable re-transmission to a chart recorder or BMS system of the flowrate.

The M800 also comes with four independent timers, which are capable of recording the total flow and peak flow with the time of occurrence within a settable period of time.

A customer selectable security code is provided to avoid casual tampering.

### Options

As well as the above functions the M800 is easily expanded by the use of additional option boards, which can be simply retrofitted to the base unit.

#### Additional options available:

- 4-20mA analog output board – providing 2 x 4-20 mA outputs, which can be configured for pressure and temperature.
- Relay option board – providing 2 x volt free relays that can be configured for alarms.
- Modbus RTU communications option board – providing access to total, flowrate, power, temperature and pressure.

### Display parameters

<b>Totalized flow</b>	scf or Nm <sup>3</sup>
<b>Flowrate</b>	scfm or Nm <sup>3</sup> /h
<b>Temperature</b>	°F or °C
<b>Pressure</b>	psi g or bar g
<b>Time</b>	24 hour clock
<b>Date</b>	MM/DD/YY or DD/MM/YY
<b>Trend graph</b>	flowrate

### Technical data - power

<b>Supply voltage</b>	99V to 264V at 50 - 60 Hz
<b>Power consumption</b>	7.5 watts maximum
<b>Overvoltage category</b>	II
<b>Pollution degree</b>	3
<b>Calculation rate</b>	10/sec (Orifice plates 2/sec)

### Technical data - input

<b>4-20 mA input(s)</b>	Input voltage (maximum)	2.5 Vdc
	Input impedance	110 Ω
	Input current (maximum)	22 mAdc
<b>Current source(s)</b>	Termination	Screw terminals (supplied)
	Resolution	0.01%
	Current output (per channel)	30 mAdc ±15%
	Open circuit voltage (maximum)	32 Vdc
	Total voltage drop (maximum)	19 Vdc @ 22 mAdc
Termination	Screw terminals (supplied)	

### Environmental information

<b>Maximum operating relative humidity</b>	80% up to 88°F (31°C) decreasing linearly to 50% at 104°F (40°C)
<b>Maximum altitude</b>	6562 ft (2000 m) above sea level
<b>Ambient temperature limits</b>	0 - 131°F (55°C)
<b>Enclosure rating</b>	IP65 (with correct cable glands)
<b>EMC: Emissions and immunity</b>	EN 61326: A1 and A2 emissions Class A equipment Table 4
	EN 61326: A1 and A2 immunity for industrial locations Annex A Table 1
<b>Electrical safety</b>	BS EN 61010-1
<b>Enclosure colours and materials</b>	Grey ABS

Local regulation may restrict the use of this product below the conditions quoted. Limiting conditions refer to standard connections only.

In the interests of development and improvement of the product, we reserve the right to change the specification.

TI-P333-24-US 08.07

## Output technical data

### Pulse output

Contacts	Volt free digital transistor (NPN or PNP)
Maximum supply voltage	28 Vdc
Maximum voltage in closed/on position	1 V
Minimum load resistor	≥ 10 kΩ
Termination	Screw terminals (supplied)

### 4 - 20 mA output

Range	4 - 20 mA
Minimum current	0 mA
Maximum current	22 mA
Open circuit voltage (maximum)	19 Vdc
Resolution	0.01%
Maximum output load	500 Ω
Isolation	100 V
Termination	Screw terminals (supplied)

## Option board technical data

### Dual relay alarm option board -

#### Two independent mains rated relay outputs

Contacts	2 x changeover relays with common
Maximum load	3 A resistive @ 250 Vac 1 A inductive @ 250 Vac
Voltage rating	250 Vdc
Electrical life	3 x 10 <sup>5</sup> or greater depending on load
Mechanical life	30 x 10 <sup>6</sup>
Termination	Screw terminals (supplied)

### Isolated dual 4 - 20 mA re-transmission option board -

#### Two independent 4 - 20 mA isolated re-transmission

Range	4 - 20 mA
Minimum current	0 mA
Maximum current	22 mA
Open circuit voltage (maximum)	18 Vdc
Resolution	0.01%
Maximum output load	500 Ω
Isolation	100 V
Termination	Screw terminals (supplied)

### Communications option board


RS485 Modbus communications	
Physical layer	4 wire full duplex or 2 wire half duplex RS485
Protocol	Modbus RTU format
Isolation	500 Vac/ dc
Receiver unit load	1/8 (256 devices maximum)
Termination	Screw terminals (supplied)

For a general description of M800 gas flowmetering systems, see other literature.

## Dimensions/weights (approximate) in inches (mm) and pounds (kg)


### Wall mounting

A	B	C	Weight
9.3 (235)	5.8 (147)	3.3 (85)	2.4 (1.1)



### Panel mounting

A	B	C	D	Weight
10 (255)	6.7 (170)	5.4 (137)	1.9 (48)	3.1 (1.4)



## Safety information, installation and maintenance

For full details, see the Installation and Maintenance Instructions supplied with the product.

### Installation notes:

**Wall mounting** 4 off screw slots in corners.

**Panel mounting** Screw in sub-assembly with back clamps.

Pre drilled knock-outs in positions shown in the IMI.

**Cable entries** Cable entry fittings and seals to suit appropriate regulations and IP rating to be supplied by the customer.

**Wiring (supplied by installer)** Total length connecting between the M800 and pipeline transmitters must not exceed 1300'(feet) (400 m). 24 AWG Wire or equivalent (signal wiring).

### How to order example:

1 off M800 wall mountable gas flow computer.