

Condensate Return and Boiler Feed Pumps "G" Series

DESCRIPTION

Spirax Sarco "G" Series condensate and boiler feed pumps are packaged units completely assembled, wired and tested at the factory. They are used in low pressure steam heating systems to collect and quickly return condensate to the boiler or boiler feed unit. Pumping action is controlled by an integral float switch on simplex (one pump) units or mechanical alternator on duplex (two pump) units. Unlike boiler feed units which are controlled by a boiler mounted control and equipped with a makeup valve mechanism, condensate pumps usually do not directly supply boiler makeup water.

AVAILABLE TYPES

Simplex units

Simplex units are equipped with vapor tight, heavy duty float switch control with stainless steel float. Easily field adjustable to provide proper pump control and operation

Duplex units

Duplex units offer some additional distinct advantages over simplex units. They are used where an unusually heavy amount of condensate must be returned or where it is desirable to have a stand-by pump available. Equipped with a float operated, automatic mechanical alternator, they provide several benefits.

- **System overload protection**—The second pump is activated if the rate of condensate return exceeds the limits of the first pump.
- Extra long service life—Each of the two pumps is activated automatically on alternating pumping cycles so the work load is evenly distributed between the two pumps.
- Back-up system protection—A second pump is automatically actuated if the first one fails to start. Maintenance or repairs can be made on either pump without shutting down the other one or interrupting system operation.

LIMITING CONDITIONS

Capacity: to 18 gpm. Discharge pressures: 20, 30 and 40 psi.

RECEIVER


Close grained cast iron. Simplex unit 6,15, 21 and 45 gallon sizes. Duplex unit 15, 21 and 45 gallon sizes.

Welded, copper bearing steel. Simplex unit 10, 20 and 45 gallon sizes. Duplex unit 20 and 45 gallon sizes.


HEAVY DUTY, DRIP PROOF MOTORS

Heavy duty, drip proof motors are designed for continuous operation. Ball bearings are prelubricated and shielded. Motors have stainless steel shaft -operated at 3450 rpm 60Hz. Both single phase115/230 volt with built-in overload protection, and three phase 230/460 volt (or 208 volt) motors are available with O.D.P. or special TEFC enclosures.

All parts of the pump and motor which are subject to normal wear are easily accessible by removal of motor and canopy, attached with universal type 4 bolt flange mounting. Service of impeller and seal is also made easy . . . entire motor can be removed without disturbing plumbing or electrical connections.



Simplex Unit



Duplex Unit

PUMP AND MOTOR ASSEMBLY

Pump and motor assembly is close coupled centrifugal design with enclosed type bronze impeller and wearing ring. The bronze impeller is designed to assure smooth, efficient water passage. No close clearances that are subject to rapid wear and reduced efficiency.

Mechanical shaft seal designed for temperatures to 250 $^{\circ}$ F. Seal is vented to receiver to insure adequate lubrication at all times.

OPTIONAL EXTRAS


Suction Isolation Valve

When installed between the pump and receiver on simplex units, it allows the pump motor assembly to be removed without draining the receiver. On duplex units, it permits one pump to be removed while the other one continues to operate without interrupting system operation.


Condensate Return and Boiler Feed Pumps "G" Series

ORDERING CODES AND MODELS

Motor		Pump		Cast Iron Receiver Sizes							Welded Steel Receiver Sizes				
Phase		Discharge		6 Gallon	15 Gallon		21 Gallon		45 Gallon		10 Gallon	20 Gallon		45 Gallon	
and	HP	Pressure	gpm	8000 EDR	1200	00 EDR	12000) EDR	12000	EDR	8000 EDR	1200	00 EDR	12000	EDR
Voltage		psi		Simplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Simplex	Duplex	Simplex	Duplex
Single	1/3	20	18	GC2S61	GC2S151	GC2D151	GC2S211	GC2D211	GC2S451	GC2D451	GS2S101	GS2S201	GS2D201	GS2S451	GS2D451
115/	1/2	30	18	GC3S61	GC3S151	GC3D151	GC3S211	GC3D211	GC3S451	GC3D451	GS3S101	GS3S201	GS3D201	GS3S451	GS3D451
230 V.	3/4	40	18	GC4S61	GC4S151	GC4D151	GC4S211	GC4D211	GC4S451	GC4D451	GS4S101	GS4S201	GS4D201	GS4S451	GS4D451
Three	1/3	20	18	GC2S63	GC2S153	GC2D153	GC2S213	GC2D213	GC2S453	GC2D453	GS2S103	GS2S203	GS2D203	GS2S453	GS2D453
230/	1/2	30	18	GC3S63	GC3S153	GC3D153	GC3S213	GC3D213	GC3S453	GC3D453	GS3S103	GS3S203	GS3D203	GS3S453	GS3D453
460 V.	3/4	40	18	GC4S63	GC4S153	GC4D153	GC4S213	GC4D213	GC4S453	GC4D453	GS4S103	GS4S203	GS4D203	GS4S453	GS4D453



DIMENSION	S (NC	MINAL) II	N INCHES	& MILLIME	TERS									
Receiver Size	A	В	С	D	E	F	G	Н	J	K	L	M	0	P
Simplex 6 gallon	1	1	2	14.5	14.5	9.5	-	-	-	9.0	-	27	-	_
	25	25	50	<i>368</i>	368	241				229		686		
Simplex 15 gallon	1	1	2	21	15.6	17.6	19.8	-	26.5	13.3	9.3	_	-	1
	25	25	50	533	396	447	503		673	338	236			25
Duplex 15 gallon	1	1	2	21.5	15.6	17.6	19.8	-	26.5	13.3	9.3	_	-	1
	25	25	50	546	396	447	503		673	338	236			25
Simplex 21 gallon	1	1-1/4	2	17	12.4	22.7	27.7	18	31.8	10.2	-	_	1.5	1.5
	25	32	50	432	315	576	704	457	808	259			38	38
Duplex 21 gallon	1	1-1/4	2	18	12.4	22.7	27.7	18	31.8	10.2	-	_	1.5	1.5
	25	32	50	457	315	576	704	457	808	259			38	38
Simplex 45 gallon	1	1-1/2	2-1/2	21.8	17.3	26.7	28.7	20	36.7	15	-	_	2.85	1
	25	38	63	554	439	678	729	508	932	381			72	25
Duplex 45 gallon	1	1-1/2	2-1/2	22.8	17.3	26.7	28.7	20	36.7	15	-	_	2.85	1
	25	38	63	579	439	678	729	508	932	381			72	25



DIMENSIONS	(иоміи	AL) IN INCHE	S & MILLIMET	ERS						
Receiver Size	A	В	С	D	E	F	G	Н	J	K
Simplex 10 gallon	1	1	2	18.2	14.2	12.5	14.3	15.2	25.2	12.7
	25	25	50	462	361	318	363	386	640	323
Simplex 20 gallon	1	1	2	18.2	14.2	22.5	24.3	15.2	25.2	12.7
	25	25	50	462	361	572	617	386	640	323
Duplex 20 gallon	1	1	2	19.7	14.2	22.5	24.3	15.2	25.2	12.7
	25	25	50	500	361	572	617	386	640	323
Simplex 45 gallon	1	1.5	3	22.4	18.4	24.4	26.4	24.4	35.4	15.7
	25	40	75	569	467	620	671	620	899	399
Duplex 45 gallon	1	1.5	3	24.4	18.4	24.4	26.4	24.4	35.4	15.7
	25	40	75	620	467	620	671	620	899	399

Spirax Sarco, Inc. 1995

TI-5-302-US 4.95
Telephone: (803) 714-2000 FAX (803) 714-2222