



# Spira-trol™ Two-port Control Valves

## EN Standard JE, JF and JL DN15 to DN200 and ASME Standard JEA, JFA and JLA 1/2" to 8"


### Description

Spira-trol™ is a range of two-port single seat globe valves with cage retained seats conforming to EN and ASME standard. These valves are available in three body materials in sizes ranging from DN15 to DN200 (1/2" to 8"). When used in conjunction with a pneumatic or electric linear actuator they provide characterized modulating or on/off control.

### Spira-trol™ valve characteristic - options:

<b>JE</b>	<b>Equal percentage (E)</b> - Suitable for most modulating process control applications providing good control at all flowrates.
<b>JF</b>	<b>Fast opening (F)</b> - For on/off applications only.
<b>JL</b>	<b>Linear (L)</b> - Primarily for liquid flow control where the differential pressures across the valve is constant.

**Important note:** Throughout this document, reference has been made to the standard JE control valve. With the exception of trim type, the JE, JF and JL control valves are identical.



### Spira-trol™ valve options:

<b>Stem sealing</b>	<b>PTFE chevron seals</b>	Standard
	<b>Graphite packing</b>	High temperature applications
	<b>Metal-to-metal</b>	431 stainless steel - standard
		316L stainless steel
<b>Seating</b>	<b>Soft seating</b>	Up to 200 °C - PTFE for Class VI shut-off
		Up to 250 °C - PEEK for Class VI shut-off
	<b>Hard facing</b>	316L stainless steel with Stellite 6 facing -for more arduous applications
<b>Bonnet type</b>	<b>Standard bonnet</b>	
	<b>Extended bonnet</b>	for large pipe lagging or hot/cold applications
<b>Trim</b>	<b>Standard trim</b>	
	<b>Low noise and anti-cavitation trim</b>	

### Spira-trol™ valves are compatible with the following actuators and positioners:

<b>Electric</b>	AEL5 and AEL6
<b>Pneumatic</b>	PN9000, TN2000 and PN1000

Refer to relevant Technical Information sheet for further details

## Standards

Designed in accordance with EN 60534. This product fully complies with the requirements of the Pressure Equipment Equipment Directive (PED) and carries the  mark when so required.

## Certification


This product is available with certification to EN 10204 3.1.

**Note:** All certification/inspection requirements must be stated at the time of order placement.

## Technical data

<b>Plug design</b>	Parabolic	
<b>Leakage</b>	Metal-to-metal	Class IV
		Class V
	Soft seal	Balanced Class IV
		Unbalanced Class VI
<b>Rangeability</b>	50:1	
<b>Travel</b>	DN15 to DN50	20 mm
	DN65 to DN100	30 mm
	DN125 to DN200	70 mm


## Typical flow characteristic curves




## Sizes and pipe connections

<b>Standard</b>	<b>EN</b>	<b>JE, JF and JL</b>	DN15, DN20, DN25, DN32, DN40, DN50, DN65, DN80, DN100, DN125, DN150 and DN200
	<b>ASME</b>	<b>JEA, JFA and JLA</b>	½", ¾", 1", 1¼", 1½", 2", 2½", 3", 4", 5", 6" and 8"
<b>Flanged</b>	<b>EN</b>	<b>Standard</b>	EN 1092 PN63 and PN100
	<b>ASME</b>	<b>Standard</b>	ASME B 16.5 Class 600, B22-20 JIS/KS 30 and JIS/KS 40
<b>Butt-weld</b>	ASME B 16.25 Schedule 40 and Schedule 80		
<b>Socket weld</b>	ASME B 16.11		
<b>Facing</b>	<b>Standard</b>		Raised face <b>Other facing</b> is available on request.
<b>Flanged face-to-face</b>	<b>EN</b>	<b>Standard</b>	EN 558 Series 2.
	<b>ASME</b>	<b>Standard</b>	ISA-S75-03.

## Materials



Standard with PTFE packing



Extended bonnet

Type	No.	Part	Material	
JE and JEA	1	Body	JE43	Carbon steel EN 10213 1.0619+N
			JEA43	Carbon steel ASTM A216 WCB
			JE63	Stainless steel EN 10213 1.4408
			JEA63	Stainless steel ASTM A351 CF8M
			JE83	Alloy steel EN 10213 1.7357
			JEA83	Alloy steel ASTM A217 WC6
	2	Cover	JE43	Carbon steel EN 10213 1.0619+N
			JEA43	Carbon steel ASTM A216 WCB
			JE63	Stainless steel EN 10213 1.4408
			JEA63	Stainless steel ASTM A351 CF8M
			JE83	Alloy steel EN 10213 1.7357
			JEA83	Alloy steel ASTM A217 WC6
	2c	Extended bonnet	JE43 and JEA43	Carbon steel A105
			JE63 and JEA63	Stainless steel A316L
			JE83 and JEA83	Stainless steel A316L

## Materials





Type	No.	Part	Material	
All versions using PTFE seals	3	Stem lock-nut	Stainless steel AISI 316	
	4	Bonnet gasket	Graphite/stainless steel	
	5	Seat retainer	Stainless steel with the exception of the full peek option	
	6	Valve seat ring	Seating version T	Stainless steel AISI 431 S29
			Seating versions P and K	PEEK
			Seating version W	Stainless Steel 316L + Stellite 6
			All others	Stainless steel 316L
	7	Seat gasket	Graphite/stainless steel	
	8	Valve plug and stem	Body stainless steel	Stainless steel with the exception of the Nitronic bush option
			All others	Stainless steel 431
	9 *	Lower stem guide	DN15 - DN100 (½" - 4")	PTFE
			DN125 - DN200 (5" - 8")	Stellite 6
	10	Lower stem wiper	DN15 - DN100 (½" - 4")	PTFE
	11	Packing guard washer	Stainless steel AISI 316L	
	12	Spring	Stainless steel BS 2056 316 S42	
	13 *	Packing spacer	Stainless steel AISI 316	
	14 *	Chevron packing set	PTFE	
	15	Outer 'O' ring	Viton	
	16	Inner 'O' ring	Viton	
	17 *	Gland flange	Stainless steel AISI 304	
	18 *	Gland follower	Stainless steel	
19	Gland nut	Stainless steel A2-70		
20	Gland stud	Stainless steel		
21	Actuator clamp nut	Plated carbon steel		
22	Bonnet nut	JE43 and JEA43	Carbon steel Grade 2H	
		JE63 and JEA63	Stainless steel Grade 8M	
		JE83 and JEA83	Alloy steel Grade 7	
23	Bonnet stud	JE43 and JEA43	Carbon steel Grade B7	
		JE63 and JEA63	Stainless steel Grade B8M2	
		JE83 and JEA83	Alloy steel Grade B16	

### \* Graphite packing

Type	No.	Part	Material
High temperature packing	9	Lower stem guide	Stellite 6
	13	Packing spacer	Stainless steel
	14	Graphoil packing	Graphite ring
	18	Gland follower	Stainless steel
	11	Not used	
	12	Not used	


### \* Graphite packing

Type	No.	Part	Material
High temperature packing	15	Not used	
	16	Not used	
	24	Extension gasket (only used with part 2c)	Graphite
	25	Extension bolting (only used with part 2c)	Stainless steel




## Pressure/temperature limits - JE43 and JEA43

PN63  
PN100



ASME 600  
JIS/KS 30  
JIS/KS 40  
Butt-weld  
Socket weld



 The product **must not** be used in this region.

 High temperature packing required for use on this region.

 Extended cover is required for use in this region.

**Notes:** 1. Where the process fluid temperature is sub-zero and the ambient temperature is below +5 °C (+41 °F), the external moving parts of the valve and actuator must be heat traced to maintain normal operation.

A - B Flanged EN 1092 PN63

A - C Flanged EN 1092 PN100

A - D Flanged JIS/KS 30


A - E Flanged JIS/KS 40

A - F Flanged ASME 600, Butt-weld and Socket weld


Body design conditions		PN100/ASME Class 600				
PMA and PMO	Maximum allowable pressure	EN	PN63	<b>JE43</b>	63 bar g @ 50 °C	
			PN100	<b>JE43</b>	100 bar g @ 50 °C	
	Maximum operating pressure	ASME 600, Butt-weld and Socket weld		<b>JEA43</b>	102.1 bar g @ 38 °C (1480 psi g @ 100 °F)	
		JIS/KS 30		<b>JEA43</b>	51 bar g @ 120 °C	
		JIS/KS 40		<b>JEA43</b>	68 bar g @ 120 °C	
Maximum differential pressure design	PTFE soft seat (G)			7 bar		
	PEEK soft seat (K)			7 bar		
	Full PEEK seat (P)			19 bar		
TMA	Maximum allowable temperature	EN		<b>JE43</b>	400 °C	
		ASME 600, Butt-weld and Socket weld		<b>JEA43</b>	425 °C (797 °F)	
		JIS/KS 30		<b>JEA43</b>	425 °C	
		JIS/KS 40		<b>JEA43</b>	425 °C	
Minimum allowable temperature					-29 °C (-20 °F)	
TMO	Maximum operating temperature (For clarification of the options G, H, K and P see the Spira-trol™ selection guide on page 9)	Standard packing PTFE chevron		(Stem sealing - Options P and N)	250 °C	
		High temperature packing		(Stem sealing - Option H)	425 °C	
		Extended bonnet (E) with PTFE chevron				250 °C
		Extended bonnet (E) with graphite packing				425 °C
		PTFE soft seat			(Seating - Option G)	200 °C
		PEEK soft seat			(Seating - Options K and P)	250 °C
Minimum operating temperature		<b>Note:</b> For lower operating temperatures consult Spirax Sarco.			-29 °C (-20 °F)	
Designed for a maximum cold hydraulic test pressure of:					156 bar g (2262 psi g)	

## Pressure/temperature limits - JE63 and JEA63


**PN63  
PN100**



**JIS/KS 30  
JIS/KS 40**



**ASME 600  
Butt-weld  
Socket weld**



- The product **must not** be used in this region.
- High temperature packing required for use on this region.
- Extended cover is required for use in this region


**Notes:** 1. Where the process fluid temperature is sub-zero and the ambient temperature is below +5 °C (+41 °F), the external moving parts of the valve and actuator must be heat traced to maintain normal operation.

- A - B Flanged EN 1092 PN63
- A - C Flanged EN 1092 PN100
- A - D Flanged JIS/KS 30
- A - E Flanged JIS/KS 40
- A - F Flanged ASME 600, Butt-weld and Socket weld


Body design conditions			PN100/ASME Class 600
PMA and PMO	Maximum allowable pressure	EN	PN63 <b>JE63</b> 63 bar g @ 100 °C
			PN100 <b>JE63</b> 100 bar g @ 100 °C
	Maximum operating pressure	ASME 600, Butt-weld and Socket weld <b>JEA63</b> 99.3 bar g @ 38 °C (1440 psi g @ 100 °F)	
		JIS/KS 30	<b>JEA63</b> 51 bar g @ 120 °C
		JIS/KS 40	<b>JEA63</b> 68 bar g @ 120 °C
Maximum differential pressure design	PTFE soft seat (G) 7 bar		
	PEEK soft seat (K) 7 bar		
	Full PEEK seat (P) 19 bar		
TMA	Maximum allowable temperature	EN	<b>JE63</b> 580 °C
		ASME 600, Butt-weld and Socket weld <b>JEA63</b> 538 °C (1000 °F)	
		JIS/KS 30	<b>JEA63</b> 490 °C
		JIS/KS 40	<b>JEA63</b> 490 °C
Minimum allowable temperature			-29 °C (-20 °F)
TMO	Maximum operating temperature (For clarification of the options G, H, K and P see the Spira-trol™ selection guide on page 9)	Standard packing PTFE chevron (Stem sealing - Options P and N)	250 °C
		High temperature packing (Stem sealing - Option H)	580 °C
		Extended bonnet (E) with PTFE chevron	250 °C
		Extended bonnet (E) with graphite packing	580 °C
		PTFE soft seat (Seating - Option G)	200 °C
		PEEK soft seat (Seating - Options K and P)	250 °C
Minimum operating temperature			<b>Note:</b> For lower operating temperatures consult SpiraxSarco. -29 °C (-20 °F)
Designed for a maximum cold hydraulic test pressure of:			156 bar g (2262 psi g)

## Pressure/temperature limits - JE83/JEA83

PN63  
PN100




JIS/KS 30  
JIS/KS 40



\* JIS/KS 40 only

ASME 600  
Butt-weld  
Socket weld



- The product **must not** be used in this region.
- High temperature packing required for use on this region.
- Extended cover is required for use in this region

**Notes:** 1. Where the process fluid temperature is sub-zero and the ambient temperature is below +5 °C (+41 °F), the external moving parts of the valve and actuator must be heat traced to maintain normal operation.

- A - B Flanged EN 1092 PN63
- A - C Flanged EN 1092 PN100
- A - D Flanged JIS/KS 30
- A - E Flanged JIS/KS 40
- A - F Flanged ASME 600, Butt-weld and Socket weld

Body design conditions		PN100/ASME Class 600			
PMA and PMO	Maximum allowable pressure	EN	PN63	<b>JE83</b>	63 bar g @ 300 °C
			PN100	<b>JE83</b>	100 bar g @ 300 °C
	Maximum operating pressure	ASME 600, Butt-weld and Socket weld		<b>JEA83</b>	103.4 bar g @ 38 °C (1499 psi g @ 100 °F)
		JIS/KS 30		<b>JEA83</b>	51 bar g @ 120 °C
		JIS/KS 40		<b>JEA83</b>	68 bar g @ 120 °C
Maximum differential pressure design	PTFE soft seat (G)			7 bar	
	PEEK soft seat (K)			7 bar	
	Full PEEK seat (P)			19 bar	
TMA	Maximum allowable temperature	EN		<b>JE83</b>	490 °C
		ASME 600, Butt-weld and Socket weld		<b>JEA83</b>	538 °C (1000 °F)
		JIS/KS 30		<b>JEA83</b>	490 °C
		JIS/KS 40		<b>JEA83</b>	510 °C
Minimum allowable temperature				-29 °C (-20 °F)	
TMO	Maximum operating temperature (For clarification of the options G, H, K and P see the Spira-trol™ selection guide on page 9)	Standard packing PTFE chevron		(Stem sealing - Options P and N)	250 °C
		High temperature packing		(Stem sealing - Option H)	538 °C
		Extended bonnet (E) with PTFE chevron			250 °C
		Extended bonnet (E) with graphite packing			538 °C
		PTFE soft seat		(Seating - Option G)	200 °C
		PEEK soft seat		(Seating - Options K and P)	250 °C
Minimum operating temperature		<b>Note:</b> For lower operating temperatures consult SpiraxSarco.		-29 °C (-20 °F)	
Designed for a maximum cold hydraulic test pressure of:				156 bar g (2262 psi g)	

## K<sub>v</sub> values

Valve size			DN15	DN20	DN25	DN32	DN40	DN50	DN65	DN80	DN100	DN125	DN150	DN200
Standard trim	High capacity	Equal %	4.9	7.2	11.0	17.5	31.0	46.0	90	115	N/A	N/A	N/A	N/A
	Full port	Equal %	4.0	6.3	10.0	16.0	25.0	36.0	63.0	100	160	245	370	580
		Linear	4.0	6.3	10.0	16.0	25.0	36.0	63.0	100	160	260	390	640
		Fast opening	4.0	6.3	10.0	18.0	28.0	50.0	85.0	117	180	260	390	640
	Reduced trim 1	Equal %	2.5	4.0	6.3	10.0	16.0	25.0	36.0	63	100	200	287	370
		Linear	2.5	4.0	6.3	10.0	16.0	25.0	36.0	63	100	200	287	550
	Reduced trim 2	Equal %	1.6	2.5	4.0	6.3	10.0	16.0	25.0	36	63	100	154	232
		Linear	1.6	2.5	4.0	6.3	10.0	16.0	25.0	36	63	100	154	232
	Reduced trim 3	Equal %	1.0	1.6	2.5	4.0	6.3	10.0	16.0	25	36	63	103	163
		Linear	1.0	1.6	2.5	4.0	6.3	10.0	16.0	25	36	63	103	163
	Reduced trim 4	Equal %		1.0	1.6		4.0	6.3		16				
		Linear		1.0	1.6		4.0	6.3		16				
	Reduced trim 5	Equal %			1.0			4.0						
		Linear			1.0			4.0						
Microflute			0.5	0.5	0.5									
			0.2	0.2	0.2									
			0.1	0.1	0.1									
			0.07	0.07	0.07									
			0.01	0.01	0.01									


Note: See TI-S24-59 for low noise and anti-cavitation trims. Special K<sub>v</sub> values are available on request.

## C<sub>v</sub> (US) values

Valve size			DN15	DN20	DN25	DN32	DN40	DN50	DN65	DN80	DN100	DN125	DN150	DN200
Standard trim	High capacity	Equal %	5.7	8.3	12.7	20.2	36.0	53.0	104.0	133.0	N/A	N/A	N/A	N/A
	Full port	Equal %	4.6	7.3	12.0	18.0	29.0	42.0	73.0	116.0	185.0	283	433	679
		Linear	4.6	7.3	12.0	18.0	29.0	42.0	73.0	116.0	185.0	300	456	749
		Fast opening	4.6	7.3	12.0	21.0	32.0	58.0	98.0	135.0	208.0	300	456	749
	Reduced trim 1	Equal %	2.9	4.6	7.3	12.0	18.0	29.0	42.0	73.0	116.0	231	336	433
		Linear	2.9	4.6	7.3	12.0	18.0	29.0	42.0	73.0	116.0	231	336	635
	Reduced trim 2	Equal %	1.8	2.9	4.6	7.3	12.0	18.0	29.0	42.0	73.0	120	154	271
		Linear	1.8	2.9	4.6	7.3	12.0	18.0	29.0	42.0	73.0	120	154	271
	Reduced trim 3	Equal %	1.2	1.8	2.9	4.6	7.3	12.0	18.0	29.0	42.0	75	154	191
		Linear	1.2	1.8	2.9	4.6	7.3	12.0	18.0	29.0	42.0	75	154	191
	Reduced trim 4	Equal %		1.2	1.8		4.6	7.3		18.0				
		Linear		1.2	1.8		4.6	7.3		18.0				
	Reduced trim 5	Equal %			1.2			4.6						
		Linear			1.2			4.6						
Microflute			0.58	0.58	0.6									
			0.23	0.23	0.23									
			0.12	0.12	0.12									
			0.081	0.081	0.081									
			0.012	0.012	0.012									

Note: See TI-S24-59 for low noise and anti-cavitation trims. Special C<sub>v</sub> values are available on request.

**Dimensions/weights (approximate) in mm and kg**



Size	Dimensions							Weights		
	A		Standard	B		C	D	ASME 600	PN100	Butt-weld Socket weld
	ASME 600 JIS/KS 30 JIS/KS 40 Butt-weld Socket weld	EN 1092 PN63 PN100		Carbon steel	Stainless steel Alloy steel					
DN15	203	210	172	261	321	64	M8	9.5	10	6
DN20	206	230	172	261	321	64	M8	10.2	12	6
DN25	210	230	172	261	321	64	M8	10.8	13	6
DN32	251	260	201	278	338	69	M8	16.5	19	11
DN40	251	260	201	278	338	69	M8	18.5	22	11
DN50	286	300	196	278	338	69	M8	22.0	27	13
DN65	311	340	282	470	587	81	M12	46.5	51	31
DN80	337	380	282	470	587	81	M12	51.5	58	35
DN100	394	430	297	513	605	81	M12	83.0	79	46
DN125	457	500	382	663	783	125	M30	133.0	124	74
DN150	508	550	400	681	801	125	M30	176.0	168	108
DN200	610	650	466	747	867	125	M30	300.0	306	197

## Spare parts

### Spira-trol™

The spare parts available are shown in solid outline. Parts drawn in a grey line are not supplied as spares.

**Note:** When placing an order for spare parts please specify clearly the full product description as found on the label of the valve body, as this will ensure that the correct spare parts are supplied.

### Available spares – JE and JEA

Actuator clamping nut		<b>A</b>
Gasket set		<b>B, G</b>
Stem seal kits	PTFE packing	<b>C</b>
	Graphite packing	<b>C1</b>
	Graphite seal set	<b>C2</b>
Plug stem and seat kit	Equal percentage trim (No gaskets supplied)	<b>D, E</b>
	Fast opening trim (No gaskets supplied)	<b>D1, E</b>
	Linear trim (No gaskets supplied)	<b>D2, E</b>
Soft seat arrangement		<b>H</b>



#### How to order spares

Always order spares by using the description given in the column headed 'Available spares', and state the size and type of valve including the full product description of the product.

**Example:** 1 - Plug stem and seat kit for a Spirax Sarco DN32 Spira-trol™ JE43PTSUSS.2 Kv 16 two-port control valve having flanged PN63 connections.

#### How to fit spares

Full fitting instructions are given in the Installation and Maintenance Instructions supplied with the spare.



## Spira-trol™ selection guide:

<b>Valve size</b>	EN standard = DN15, DN20, DN25, DN32, DN40, DN50, DN65*, DN80, DN100, DN125, DN150, DN200 ASME standard = ½", ¾", 1", 1¼", 1½", 2", 2½", 3", 4", 5", 6" and 8"	<b>DN25</b>
<b>Valve series</b>	J = J series 2-port control valve	<b>J</b>
<b>Valve characteristic</b>	E = Equal percentage F = Fast opening L = Linear	<b>E</b>
<b>Flange type</b>	Blank = EN (PN) A = ASME	<b>Blank</b>
<b>Flow</b>	Blank = under T = over	<b>Blank</b>
<b>Body material</b>	4 = Carbon steel 6 = Stainless steel 8 = Alloy steel	<b>4</b>
<b>Connections</b>	1 = Screwed 2 = Socket weld 3 = Flanged 4 = Butt weld	<b>3</b>
<b>Stem sealing</b>	H = Graphite N = PTFE and Nitronic bearing (Available for DN15 to DN50 size range only) P = PTFE V = PTFE for Vacuum	<b>P</b>
<b>Seating</b>	G = PTFE soft seat K = PEEK soft seat P = Full PEEK S = 316L stainless steel (Available for DN15 to DN100 size range only) T = 431 stainless steel W = 316L with stellite 6 facing	<b>T</b>
<b>Type of trim</b>	A1 = 1 stage anti-cavitation A2 = 2 stage anti-cavitation P1 = 1 stage low noise trim P2 = 2 stage low noise trim P3 = 3 stage low noise trim S = Standard trim	<b>S</b>
<b>Trim balancing</b>	B = Balanced U = Unbalanced	<b>U</b>
<b>Bonnet type</b>	E = Extended S = Standard	<b>S</b>
<b>Bolting</b>	S = Standard	<b>S</b>
<b>Series</b>	2 = .2	<b>0.2</b>
<b>Kv</b>	To be specified	<b>Kv 10</b>
<b>Connection type</b>	To be specified	<b>Flanged PN63</b>

\* **Please note:** The PN63 flanges for the JE43 sizes have 4 bolt holes as standard; 8 bolt holes are available on request.

### Selection example:

DN32	-	J	E	4	3	P	T	S	U	S	S	.2	-	Kv 16	-	Flanged PN63
------	---	---	---	---	---	---	---	---	---	---	---	----	---	-------	---	--------------

### How to order

**Example:** 1 off Spirax Sarco Spira-trol™ DN32 JE43PTSUSS.2 Kv 16 two-port control valve having flanged PN63 connections.