



## Control Panels SSCRU Series

### Available configurations

|                     |   |
|---------------------|---|
| Panel type          | Simplex Condensate Panel  |
|                     | Duplex Condensate Panel – Mechanical Alternator                   |
|                     | Duplex Condensate Panel – Electric Alternator                     |
| Electric voltage    | 115V, 208V, 230V, 460V, 575V                                      |
| Enclosure           | NEMA N3R, NEMA N4, NEMA N4XFG, NAME N4XSS, NEMA N12               |
| Shipment            | Mounted and Wired or Shipped Loose for Remote Mounting            |
| Standard components | Motor Starters & Overloads (Duplex)                               |
|                     | Pump Circuit Breaker(s)   |
|                     | HOA Selector Switch(es)   |
|                     | Pump Run Indicator Light(s)                                       |
|                     | Control Circuit Transformer                                       |
| Panel options       | Fused or Non-Fused Disconnects                                    |
|                     | High/Low Level Alarm Circuits                                     |
|                     | Elapsed Run Time Meter  |
|                     | Resettable Elapsed Run Time Meter                                 |
|                     | Cycle Counter   |
|                     | Push to Test Button   |
|                     | Lead Pump Selector/Transfer Switch                                |
|                     | Dry Contact(s) for Building Management System (BMS) Compatibility |

### NEMA Enclosure Ratings

| Enclosure Rating | Definition                |   |
|------------------|---------------------------|---|
| NEMA Type 1      | General-purpose           | Protects against dust, light, and indirect splashing but is not dust-tight; primarily prevents contact with live parts; used indoors and under normal atmospheric conditions. |
| NEMA Type 3R     | Intended for outdoor use  | Provides a degree of protection against falling rain and ice formation. Meets rod entry, rain, external icing, and rust-resistance design tests.                              |
| NEMA Type 4, 4X  | Watertight (weatherproof) | Designed for indoor or outdoor use, provides a degree of protection against corrosion, windblown dust & rain, splashing water, and damage from external ice formation.        |
| NEMA Type 12     | General-purpose           | Intended for indoor use, provides some protection against dust, falling dirt, and dripping noncorrosive liquids. Meets drip, dust, and rust resistance tests.                 |