

EU - Type examination certificate

According to module B (production type) annex III of directive 2014/68/EU

applicant: Spirax Sarco GmbH, Reichenaustr. 210
D – 78467 Konstanz

manufacturing site: see applicant

Type, model: Actuators for water and steam as equipment part
with safety function
Actuator type: EL5060(P)
with actuators: SPIRA-TROL K... and L...
Type designation: KE... and LE...
List of types see appendix.

Category per annex II: IV

Type examination report-no.: **20180918-28366-1893104196-100-421411-PB**

Basis of testing: DIN EN 14597 : 2015-02 Ann. DX

The above-mentioned product complies with the relevant provisions of the council directive of 15 May 2014 on the approximation of the laws of the member states concerning pressure equipment (2014/68/EU).

A list of all technical documents is attached as an integral part.


Notified body: 2266

This certificate is valid until: 2028-05-14

Certificate registration no.: Z-D-002-12288/18

This certificate expires latest by the date shown above unless the legal basis changes. In that case DEKRA Automobil GmbH will inform you of such changes. DEKRA Automobil GmbH reserves the right to impose additional tests in case of a change in the legal basis. DEKRA Automobile GmbH may limit the scope, suspend or revoke this certificate in justified cases. The holder of this certificate has the right to appeal any of the decisions made by DEKRA Automobil GmbH by filing a written complaint submitted to the regional technical center in charge. The holder of this certificate is obligated to apply for approval of any changes to the design of above mentioned type in writing to the regional technical center in charge prior implementation.

Stuttgart, 2018-09-19


Zertifizierungsstelle für Druckgeräte



DEKRA Automobil GmbH, Handwerkstraße 15, D-70565 Stuttgart
Tel.: 0711.78 61-25 56 Fax: 0711.78 61-27 17
www.dekra.com

Annex to Module Modul B – Z-D-002-12288 / 18, page 1

This certificate is valid for the following versions:

Type	DN	PN	Material	Sealing system	Temperature-range of the medium in °C	Stem seal
KE 43	15 - 100	40	Cast steel	metallic sealing	10 - 250	PTFE ring packing
KE 63	15 - 100	40	Stainless steel	metallic sealing	10 - 250	PTFE ring packing
KE 73	15 - 100	25	Ductile iron	metallic sealing	10 - 250	PTFE ring packing
KE 73	65 - 100	16	Ductile iron	metallic sealing	10 - 250	PTFE ring packing
LE 33	15 - 100	16	Cast iron	metallic sealing	10 - 250	PTFE ring packing
LE 43	15 - 100	16	Cast steel	metallic sealing	10 - 250	PTFE ring packing
LE 63	15 - 100	16	Stainless steel	metallic sealing	10 - 250	PTFE ring packing