




Spira-trol™ Two-port Control Valves

EN Standard LE, LF and LL DN15 to DN100 and ASME Standard LEA, LFA and LLA ½" to 4"

Description

Spira-trol™ is a range of two-port single seat globe valves with cage retained seats conforming to EN and ASME standard. These valves are available in three body materials in sizes ranging from DN15 to DN100 (½" to 4"). When used in conjunction with a pneumatic or electric linear actuator they provide characterized modulating or on/off control.



Sizes and pipe connections

Body material	Connections	Type	Size range
Cast iron	Screwed	BSP	LE31 DN15, DN20, DN25, DN32, DN40 and DN50
		NPT	LEA31 ½", ¾", 1", 1¼", 1½" and 2"
	Flanged	EN 1092 PN16, JIS/KS 10	LE33
ASME class 125		LEA33	1", 1½", 2", 2½", 3" and 4"
Carbon steel	Flanged	EN 1092 PN16, JIS/KS 10	LE43 DN15, DN20, DN25, DN32, DN40, DN50, DN65, DN80 and DN100
		ASME class 150	LEA43 ½", ¾", 1", 1½", 2", 2½", 3" and 4"
		JIS/KS 10	LEA43
Stainless steel	Flanged	EN 1092 PN16, JIS/KS 10	LE63 DN15, DN20, DN25, DN32, DN40, DN50, DN65, DN80 and DN100
		ASME class 150	LEA63 ½", ¾", 1", 1½", 2", 2½", 3" and 4"
		JIS/KS 10	LEA63

Spira-trol valve characteristic - options:

LE and LEA Equal percentage (E) - Suitable for most modulating process control applications providing good control at all flowrates.

LF and LFA Fast opening (F) - For on/off applications only.

LL and LLA Linear (L) - Primarily for liquid flow control where the differential pressures across the valve is constant.

Important note: Throughout this document, reference has been made to the standard LE or LEA control valve. With the exception of trim type, the LE, LEA, LF, LFA, LL and LLA control valves are identical.

Spira-trol valve options:

Stem sealing	PTFE chevron seals	Standard
	Bellows/graphite secondary seals (D)	Zero emissions and high temperature applications
	Graphite packing	High temperature applications
Seating	Metal-to-metal	431 stainless steel - standard
		316L stainless steel
	Soft seating	Up to 200 °C (392 °F) - PTFE for Class VI shut-off
		Up to 250 °C (482 °F) - PEEK for Class VI shut-off
Hard facing	316L stainless steel with Stellite 6 facing - for more arduous applications	
Bonnet type	Standard bonnet	
	Extended bonnet for large pipe lagging or hot/cold applications	
Trim	Standard trim	
	Low noise and anti-cavitation trim (see TI-S24-59)	

Spira-trol valves are compatible with the following actuators and positioners:

Electric AEL3, AEL5 and AEL6 series

Pneumatic PN1000, PN9000, PN2000, TN2000 and TN2100 Series

Refer to the relevant Technical Information sheet for further details.

Standards

Designed in accordance with EN 60534. This product fully complies with the requirements of the Pressure Equipment Directive and carries the  mark when so required.

Certification


This product is available with certification to EN 10204 3.1.

Note: All certification/inspection requirements must be stated at the time of order placement.

Technical data

Plug design		Parabolic	
Leakage	Metal-to-metal	Balanced and Unbalanced	Class IV
		Unbalanced	(optional) Class V
	Soft seal	Balanced	Class IV
		Unbalanced	Class VI
Rangeability	Equal	50:1	
	Linear	30:1	
	Fast	10:1	
Travel	DN15 - DN50 (½" - 2")	20 mm (¾")	
	DN65 - DN100 (2½" - 4")	30 mm (1¼")	



Typical flow characteristic curves



Materials

Body material	No.	Part	Type	Material	
Cast iron	1	Body	LE31 and LE33	SG iron EN 1563 : EN-GJS-400-18	
			LEA31 and LEA33	Cast iron ASTM A126B	
	2	Bonnet	DN15 - DN50 (½" - 2")	LE31 and LE33	SG iron EN 1563 : EN-GJS-400-18
				LEA31 and LEA33	Ductile iron ASTM A395
			DN65 - DN100 (2½" - 4")	LE31 and LE33	Cast iron EN 1561 : EN-GJL-250
				LEA31 and LEA33	Ductile iron ASTM A395
2a	Bonnet extension	LE31 and LE33	Carbon steel EN 10213 GP240GH+N (1.0619N) ASTM A216 WCB or A105N		
		LEA31 and LEA33			
Carbon steel	1	Body	LE43	Carbon steel EN 10213 GP240GH+N (1.0619N)	
			LEA43	Cast steel ASTM A216 WCB	
	2	Bonnet	DN15 - DN50 (½" - 2")	LE43	Carbon steel EN 10273 P250GH (1.0460)
				LEA43	Carbon steel ASTM A105N
			DN65 - DN100 (2½" - 4")	LE43	Steel EN10213 GP240GH+N (1.0619N)
				LEA43	Cast steel ASTM A216 WCB
2a	Bonnet extension	LE43 and LEA43	Carbon steel EN 10213 GP240GH+N (1.0619N) ASTM A216 WCB or A105N		
Stainless steel	1	Body	LE63	Stainless steel EN 10213 1.4408 ASTM A351 CF8M	
			LEA63		
	2	Bonnet	LE63	Stainless steel EN 10213 1.4408 ASTM A351 CF8M	
			LEA63		
2a	Bonnet extension	LE63 and LEA63	Stainless steel AISI 316L		
All versions	2b	Bellows	All versions	Stainless steel AISI 316L	
	2c	Extended bonnet	LE63 and LEA63	Stainless steel A351 CF8M and EN 10213 1.4408	
			All others	Carbon steel A216 WCB and EN 10213 1.0619N	
	3	Stem lock-nut	All versions	Stainless steel AISI 431	
	4	Bonnet gasket	All versions	Reinforced exfoliated graphite	
	5	Seat retainer	All versions	Stainless steel AISI 316L	
	6	Valve seat ring	Seating version T	Stainless steel AISI 431	
			Seating versions P and K	PEEK	
			All others	Stainless steel AISI 316L	
	7	Seat gasket	Seating version W	Stellite Alloy 6	
	8	Valve plug and stem	All versions	Reinforced exfoliated graphite	
			All others	Stainless steel AISI 431	
			LE63	Stainless steel AISI 316L	
	9 *	Lower stem guide	All versions	Glass filled PTFE, except Nitronic bush option	
	10 *	Lower stem wiper	All versions	PTFE	
	11 *	Packing guard washer	All versions	Stainless steel AISI 316L	
	12 *	Spring	All versions	Stainless steel AISI 316L	
	13	Packing spacer	All versions	Stainless steel AISI 316L	
	14 *	Chevron packing set	All versions	PTFE	
	15 *	Outer 'O' ring	All versions	Viton	
	16 *	Upper stem guide	All versions	Glass filled PTFE, except Nitronic bush option	
	17 *	Inner 'O' ring	All versions	Viton	
	18	Gland nut	All others	Stainless steel AISI 431 AISI 316L	
			LE63		
	19	Scraper ring	All versions	PTFE	
	20	Actuator clamp nut	All versions	Plated carbon NFA 35553 XC 18	
	21	Bellows assembly	All versions	Stainless steel	
	22	Bonnet extension gasket	All versions	Reinforced exfoliated graphite	
23	Top plate (bonnet extension only)	All versions	Stainless steel AISI 316L		
24	Lower spindle bearing housing	All versions	Stainless steel AISI 316L		
25	Lower spindle bearing	All versions	Stainless steel AISI 431		
		Without stainless steel	Stellite Alloy 6		
26	Spindle lock and anti-rotation nut	All versions	Stainless steel		
27	Bonnet nuts	LEA63	Stainless steel ASTM A194 Gr. 8M		
		All others	Steel ASTM A194 Gr. 2H		
		LE63	Stainless steel A2-70		
27	Set screws	All others	Steel 8.8		
		LEA63	Stainless steel ASTM A193 Gr. B8 M2		
28	Standard bonnet studs	All others	Steel ASTM A193 Gr. B7		

LE valve with PTFE packing





Bonnet with graphite packing


*** Graphite packing**

Body material	No.	Part	Material
High temperature packing	9 16	Lower and upper stem guide	Stellite 6
	14	Grafoil packing	Graphite rings
	10, 11, 12, 15, 17, 19		Not used


LEA valve with extended bonnet (E)



*** PTFE stem sealing**



PTFE stem sealing for vacuum service



K_v values

Valve size			DN15 (½")	DN20 (¾")	DN25 (1")	DN32 (1¼")	DN40 (1½")	DN50 (2")	DN65 (2½")	DN80 (3")	DN100 (4")	
Standard trim	High capacity	Equal %	4.9	7.2	11.0	17.5	31.0	46.0	90	115	N/A	
		Full port	Equal %	4.0	6.3	10.0	16.0	25.0	36.0	63	100	160
	Full port	Linear	4.0	6.3	10.0	16.0	25.0	36.0	63	100	160	
		Fast opening	4.0	6.3	10.0	18.0	28.0	50.0	85	117	180	
	Reduced trim 1	Equal %	2.5	4.0	6.3	10.0	16.0	25.0	36	63	100	
		Linear	2.5	4.0	6.3	10.0	16.0	25.0	36	63	100	
	Reduced trim 2	Equal %	1.6	2.5	4.0	6.3	10.0	16.0	25	36	63	
		Linear	1.6	2.5	4.0	6.3	10.0	16.0	25	36	63	
	Reduced trim 3	Equal %	1.0	1.6	2.5	4.0	6.3	10.0	16	25	36	
		Linear	1.0	1.6	2.5	4.0	6.3	10.0	16	25	36	
	Reduced trim 4	Equal %		1.0	1.6		4.0	6.3		16		
		Linear		1.0	1.6		4.0	6.3		16		
	Reduced trim 5	Equal %			1.0			4.0				
		Linear			1.0			4.0				
	Microflute			0.5	0.5	0.5						
				0.2	0.2	0.2						
			0.1	0.1	0.1							
			0.07	0.07	0.07							
			0.01	0.01	0.01							

Notes:

- Special K_v on request
- For low noise and anticavitation K_v please see TI-S24-59

C_v (US) values

$$C_v (US) = C_v (UK) \times 1.2009$$


Valve size			DN15 (½")	DN20 (¾")	DN25 (1")	DN32 (1¼")	DN40 (1½")	DN50 (2")	DN65 (2½")	DN80 (3")	DN100 (4")	
Standard trim	High capacity	Equal %	5.7	8.3	12.7	20.2	36.0	53.0	104.0	133.0	N/A	
		Full port	Equal %	4.6	7.3	12.0	18.0	29.0	42.0	73.0	116.0	185.0
	Full port	Linear	4.6	7.3	12.0	18.0	29.0	42.0	73.0	116.0	185.0	
		Fast opening	4.6	7.3	12.0	21.0	32.0	58.0	98.0	135.0	208.0	
	Reduced trim 1	Equal %	2.9	4.6	7.3	12.0	18.0	29.0	42.0	73.0	116.0	
		Linear	2.9	4.6	7.3	12.0	18.0	29.0	42.0	73.0	116.0	
	Reduced trim 2	Equal %	1.8	2.9	4.6	7.3	12.0	18.0	29.0	42.0	73.0	
		Linear	1.8	2.9	4.6	7.3	12.0	18.0	29.0	42.0	73.0	
	Reduced trim 3	Equal %	1.2	1.8	2.9	4.6	7.3	12.0	18.0	29.0	42.0	
		Linear	1.2	1.8	2.9	4.6	7.3	12.0	18.0	29.0	42.0	
	Reduced trim 4	Equal %		1.2	1.8		4.6	7.3		18.0		
		Linear		1.2	1.8		4.6	7.3		18.0		
	Reduced trim 5	Equal %			1.2			4.6				
		Linear			1.2			4.6				
	Microflute			0.58	0.58	0.6						
				0.23	0.23	0.23						
			0.12	0.12	0.12							
			0.081	0.081	0.081							
			0.012	0.012	0.012							

Notes:

- Special C_v on request
- For low noise and anticavitation C_v please see TI-S24-59

Pressure/temperature limits - LE31 and LE33 cast iron valve body


Screwed BSP Flanged EN 1092 PN16



Note:

When the process fluid temperature is sub-zero and the ambient temperature is below +5 °C, the external moving parts of the valve and actuator must be heat traced to maintain normal operation.

Flanged JIS/KS 10




- The product **must not** be used in this region.
- High temperature graphite packing is required for use in this region.
Note: Soft seated valves cannot be used in this region.
- PTFE soft seated valves are limited to a maximum operating temperature of 200 °C.

Body design conditions	PN16	
Maximum design pressure	16 bar g @ 120 °C	
Maximum design temperature	300 °C @ 9.6 bar g	
Maximum differential pressure design	PTFE soft seat (G)	7 bar
	PEEK soft seat (K)	7 bar
	Full PEEK seat (P)	19 bar
Minimum design temperature	-10 °C	
Maximum operating temperature	Standard packing PTFE chevron - Option P or N	250 °C
	PTFE soft seat - Option G	200 °C
	PEEK soft seat - Option K or P	250 °C
	Graphite packing - Option H	300 °C
	Extended bonnet with PTFE chevron - Option E	250 °C
See the Spira-trol™ selection guide on page 18 for the full list of available options	Extended bonnet with graphite packing - Option E	300 °C
	Bellows - Option D	300 °C
Minimum operating temperature	Note: For lower operating temperatures consult Spirax Sarco	-10 °C
Maximum differential pressures	See relevant actuator Technical Information sheet.	
Maximum cold hydraulic test pressure of:	24 bar g	

Pressure/temperature limits - LE43 carbon steel valve body


Flanged EN 1092 PN16



Please note - Bellows sealed valves (Option **D**) are limited to **A - A**.

Note: When the process fluid temperature is sub-zero and the ambient temperature is below +5 °C, the external moving parts of the valve and actuator must be heat traced to maintain normal operation.

Flanged JIS/KS 10




- The product **must not** be used in this region.
- High temperature graphite packing is required for use in this region.
Note: Soft seated valves cannot be used in this region.
- PTFE soft seated valves are limited to a maximum operating temperature of 200 °C.

Body design conditions		PN16
Maximum design pressure		16 bar g @ 50 °C
Maximum design temperature		400 °C @ 9.5 bar g
Maximum differential pressure design	PTFE soft seat (G)	7 bar
	PEEK soft seat (K)	7 bar
	Full PEEK seat (P)	19 bar
Minimum design temperature		-10 °C
Maximum operating temperature	Standard packing PTFE chevron - Option P or N	250 °C
	PTFE soft seat - Option G	200 °C
	PEEK soft seat - Option K or P	250 °C
	Graphite packing - Option H	400 °C
See the Spira-trol™ selection guide on page 18 for the full list of available options	Extended bonnet with PTFE chevron - Option E	250 °C
	Extended bonnet with graphite packing - Option E	400 °C
	Bellows (A - A on the LE43 chart) - Option D	300 °C
Minimum operating temperature	Note: For lower operating temperatures consult Spirax Sarco	-10 °C
Maximum differential pressures	See relevant actuator Technical Information sheet.	
Maximum cold hydraulic test pressure of:		24 bar g

For valve operating above 300 °C extended bonnet is recommended for actuator suitability.

Pressure/temperature limits - LE63 stainless steel valve body


Flanged EN 1092 PN16



Please note - Bellows sealed valves (Option **D**) are limited to **A - A**.

Note: When the process fluid temperature is sub-zero and the ambient temperature is below +5 °C, the external moving parts of the valve and actuator must be heat traced to maintain normal operation.

Flanged JIS/KS 10




- The product **must not** be used in this region.
- High temperature graphite packing is required for use in this region.
Note: Soft seated valves cannot be used in this region.
- PTFE soft seated valves are limited to a maximum operating temperature of 200 °C.

Body design conditions	PN16	
Maximum design pressure	16 bar g @ 50 °C	
Maximum design temperature	400 °C @ 10.9 bar g	
Maximum differential pressure design	PTFE soft seat (G)	7 bar
	PEEK soft seat (K)	7 bar
	Full PEEK seat (P)	19 bar
Minimum design temperature	-10 °C	
Maximum operating temperature	Standard packing PTFE chevron - Option P or N	250 °C
	PTFE soft seat - Option G	200 °C
	PEEK soft seat - Option K or P	250 °C
	Graphite packing - Option H	400 °C
See the Spira-trol™ selection guide on page 18 for the full list of available options	Extended bonnet with PTFE chevron - Option E	250 °C
	Extended bonnet with graphite packing - Option E	400 °C
	Bellows (A - A on the LE63 chart) - Option D	300 °C
Minimum operating temperature Note: For lower operating temperatures consult Spirax Sarco	PTFE packing	-28 °C
	Graphite packing	-10 °C
Maximum differential pressures	See relevant actuator Technical Information sheet.	
Maximum cold hydraulic test pressure of:	24 bar g	

For valve operating above 300 °C extended bonnet is recommended for actuator suitability.


Pressure/temperature limits - LEA31 and LEA33 cast iron valve body

Screwed NPT
Flanged
ASME class 125



Note:
When the process fluid temperature is sub-zero and the ambient temperature is below +5 °C (41 °F), the external moving parts of the valve and actuator must be heat traced to maintain normal operation.

Flanged
JIS/KS 10




 The product **must not** be used in this region.

 PTFE soft seated valves are limited to a maximum operating temperature of 200 °C.

Body design conditions		ASME 125
Maximum design pressure		13.7 bar g @ 65 °C (200 psi g @ 150 °F)
Maximum design temperature		232 °C @ 8.6 bar g (450 °F @ 125 psi g)
Maximum differential pressure design	PTFE soft seat (G)	7 bar
	PEEK soft seat (K)	7 bar
	Full PEEK seat (P)	19 bar
Minimum design temperature		-29 °C (-20 °F)
Maximum operating temperature	Standard packing PTFE chevron - Option P or N	232 °C (450 °F)
	PTFE soft seat - Option G	200 °C (392 °F)
	PEEK soft seat - Option K or P	232 °C (450 °F)
	Graphite packing - Option H	232 °C (450 °F)
See the Spira-trol™ selection guide on page 18 for the full list of available options	Extended bonnet with PTFE chevron - Option E	232 °C (450 °F)
	Extended bonnet with graphite packing - Option E	232 °C (450 °F)
	Bellows - Option D	232 °C (450 °F)
Minimum operating temperature	Note: For lower operating temperatures consult Spirax Sarco	-29 °C (-20 °F)
Maximum differential pressures	See relevant actuator Technical Information sheet.	
Maximum cold hydraulic test pressure of:	21 bar g	(300 psi g)

Pressure/temperature limits - LEA43 carbon steel valve body


Flanged ASME class 150



Please note - Bellows sealed valves (Option **D**) are limited to **A - A**.

Note: When the process fluid temperature is sub-zero and the ambient temperature is below +5 °C (41 °F), the external moving parts of the valve and actuator must be heat traced to maintain normal operation.

Flanged JIS/KS 10




- The product **must not** be used in this region.
- High temperature graphite packing is required for use in this region.
Note: Soft seated valves cannot be used in this region.
- PTFE soft seated valves are limited to a maximum operating temperature of 200 °C (482 °F).

Body design conditions		ASME 150	
Maximum design pressure		19.6 bar g @ 38 °C (285 psi g @ 100 °F)	
Maximum design temperature		425 °C @ 5.5 bar g (800 °F @ 80 psi g)	
Maximum differential pressure design	PTFE soft seat (G)	7 bar	
	PEEK soft seat (K)	7 bar	
	Full PEEK seat (P)	19 bar	
Minimum design temperature		-29 °C (-20 °F)	
Maximum operating temperature	Standard packing PTFE chevron - Option P or N	250 °C (482 °F)	
	PTFE soft seat - Option G	200 °C (392 °F)	
	PEEK soft seat - Option K or P	250 °C (482 °F)	
	Graphite packing - Option H	425 °C (800 °F)	
See the Spira-trol™ selection guide on page 18 for the full list of available options	Extended bonnet with PTFE chevron - Option E	250 °C (482 °F)	
	Extended bonnet with graphite packing - Option E	425 °C (800 °F)	
	Bellows (A - A on the LEA43 chart) - Option D	300 °C (572 °F)	
Minimum operating temperature	Note: For lower operating temperatures consult Spirax Sarco	-29 °C (-20 °F)	
Maximum differential pressures	See relevant actuator Technical Information sheet.		
Maximum cold hydraulic test pressure of:	29.5 bar g		(428 psi g)

For valve operating above 572 °F (300 °C) extended bonnet is recommended for actuator suitability.

Pressure/temperature limits - LEA63 stainless steel valve body


Flanged ASME class 150



Please note - Bellows sealed valves (Option **D**) are limited to **A - A**.

Note: When the process fluid temperature is sub-zero and the ambient temperature is below +5 °C (41 °F), the external moving parts of the valve and actuator must be heat traced to maintain normal operation.

Flanged JIS/KS 10




- The product **must not** be used in this region.
- High temperature graphite packing is required for use in this region.
Note: Soft seated valves cannot be used in this region.
- PTFE soft seated valves are limited to a maximum operating temperature of 200 °C (482 °F).

Body design conditions		ASME 150	
Maximum design pressure		19.6 bar g @ 38 °C (275 psi g @ 100 °F)	
Maximum design temperature		538 °C @ 1.3 bar g (1 000 °F @ 20 psi g)	
Maximum differential pressure design	PTFE soft seat (G)	7 bar	
	PEEK soft seat (K)	7 bar	
	Full PEEK seat (P)	19 bar	
Minimum design temperature		-29 °C (14 °F)	
Maximum operating temperature	Standard packing PTFE chevron - Option P or N	250 °C (482 °F)	
	PTFE soft seat - Option G	200 °C (392 °F)	
	PEEK soft seat - Option K or P	250 °C (482 °F)	
	Graphite packing - Option H	538 °C (1 000 °F)	
See the Spira-trol™ selection guide on page 18 for the full list of available options	Extended bonnet with PTFE chevron - Option E	250 °C (482 °F)	
	Extended bonnet with graphite packing - Option E	538 °C (1 000 °F)	
	Bellows (A - A on the LEA63 chart) - Option D	300 °C (572 °F)	
Minimum operating temperature Note: For lower operating temperatures consult Spirax Sarco	PTFE packing	-29 °C (14 °F)	
	Graphite packing	-29 °C (14 °F)	
Maximum differential pressures See relevant actuator Technical Information sheet.			
Maximum cold hydraulic test pressure of:		28.4 bar g	(413 psi g)


For valve operating above 572 °F (300 °C) extended bonnet is recommended for actuator suitability.

Dimensions for the **Spira-trol™ two-port control valve** approximate in mm and (inches)


Valve size	Screwed						Flanged					D	E	F		
	BSP			NPT			LE valves			LEA valves				Thread	Bellows seals	Extended bonnet
	A	B	C	A	B	C	PN16	A1	C1	A1	C1					
								JIS/KS LE43 LE63								
DN15 (½")	130	40	103	165 (6½")	44 (1¼")	102 (4")	130	123	103	184 (7¼")	102 (4")	69 (2¾")	M8	237 (9")	336 (13.25")	
DN20 (¾")	155	45	103	165 (6½")	44 (1¼")	102 (4")	150	144	103	184 (7¼")	102 (4")			237 (9")	336 (13.25")	
DN25 (1")	160	50	103	197 (7¾")	57 (2¼")	102 (4")	160	160	103	184 (7¼")	102 (4")			237 (9")	336 (13.25")	
DN32 (1¼")	185	60	132	216 (8½")	57 (2¼")	127 (5")	180	176	132	222 (8¾")	127 (5")			267 (10½")	354 (13.94")	
DN40 (1½")	205	65	132	235 (9¼")	63 (2½")	127 (5")	200	198	132	222 (8¾")	127 (5")			267 (10½")	354 (13.94")	
DN50 (2")	230	80	127	267 (10½")	76 (3")	127 (5")	230	222	127	254 (10")	127 (5")			267 (10½")	354 (13.94")	
DN65 (2½")							290	290	200	276 (10½")	200 (7⅞")	81 (3")	M12	368 (14½")	416 (16.38")	
DN80 (3")							310	310	200	298 (11¾")	200 (7⅞")			368 (14½")	416 (16.38")	
DN100 (4")							350	350	216	352 (13¾")	216 (8½")			381 (15")	431 (17")	



Screwed version



Flanged version




Bellows sealed or extended bonnet version

Weights for the **Spira-trol™ two-port control valve** approximate in kgs (and lbs)

Valve size	LE31	LE33	LE43	LE63	LEA31	LEA33	LEA43	LEA63	Additional bellows and Extended bonnet
DN15 (½)	4.0	5.0	5.0	5.0	7.3 (16)	7.3 (16)	7.3 (16)	7.3 (16)	4.5 (10)
DN20 (¾)	5.0	6.0	6.0	6.0	7.3 (16)	8.2 (18)	8.2 (18)	8.2 (18)	
DN25 (1)	5.5	6.5	6.5	6.5	10 (22)	13.6 (30)	13.6 (30)	13.6 (30)	
DN32 (1¼)	9.0	10.0	10.0	10.0	11.3 (25)	13.2 (29)	14.1 (31)	14.1 (31)	5.5 (12)
DN40 (1½)	10.0	12.8	12.8	12.8	14.1 (31)	14.1 (31)	16.3 (36)	16.3 (36)	
DN50 (2)	11.0	15.0	15.0	15.0	15 (33)	17.2 (38)	17.2 (38)	17.2 (38)	
DN65 (2½)		32.0	32.0	32.0		38 (84)	35 (78)	35 (78)	10.0 (21)
DN80 (3)		36.0	36.0	36.0		41 (91)	40 (89)	40 (89)	
DN100 (4)		53.0	53.0	53.0		60 (132)	56 (124)	56 (124)	13.0 (28)

Dimensions/weights for the **PN actuator range** approximate in mm and kgs (inches and lbs)

Actuator range	F		G		H		J		Weight			
	mm	inches	mm	inches	mm	inches	mm	inches	Actuator		With handwheel	
									kg	lbs	kg	lbs
PN1500 and PN2500	405	16"	1114	46"					55	121.00		
PN1600 and PN2600	465	18 5/16"	1116	46"					70	154.00		
PN9100E and variants	170	6 11/16"	275	10 7/8"	55	2 3/16"	225	8 7/8"	6	13.25	+5.86	+13.00
PN9100R and variants					140	5 1/2"					+2.50	+5.50
PN9200E and variants	300	11 7/8"	300	11 7/8"	55	2 3/16"	225	8 7/8"	17	37.50	+7.20	+15.75
PN9200R and variants					140	5 1/2"					+3.77	+8.50
PN9320E and variants	390	15 9/16"	325	12 7/8"	65	2 9/16"	350	13 3/4"	27	59.50	+7.20	+15.75
PN9320R and variants					150	15 7/8"					+3.77	+8.50
PN9330E and variants	390	15 9/16"	335	13 3/8"	65	2 9/16"	350	13 3/4"	27	59.50	+7.20	+15.75
PN9330R and variants					150	15 7/8"					+3.77	+8.50



Dimensions/weights for the **AEL actuator ranges** approximate in mm and kgs (inches and lbs)

Actuator range	F		G		Weight	
	mm	inches	mm	inches	kg	lbs
AEL3	230 x 149	9" x 6"	283	11 1/4"	5.7	12.5
AEL55 and AEL65	180	7"	557	22"	10.0	22.0
AEL51, AEL52, AEL53, AEL62 and AEL63	177	7"	459	18"	5.0	11.0
AEL54 and AEL64	177	7"	490	19"	7.0	15.5
AEL56 and AEL66	226	9"	760	30"	20.0	44.0

Spare parts

Spira-trol™ - L series

The spare parts available are shown in solid outline. Parts drawn in a grey line are not supplied as spares.

Note: When placing an order for spare parts please specify clearly the full product description as found on the label of the valve body, as this will ensure that the correct spare parts are supplied.

Available spares

Actuator clamping nut		A
Gasket set	(Non-bellows sealed)	B, G
	PTFE packing	C
Stem seal kits	Graphite packing	C1
	Graphite seal set	C2
Plug stem and seat kit (No gaskets supplied)		D, E
		H
PTFE or PEEK soft seat seal		B, G, C1
		B, G, C
Stem packing and gasket		B, G, C2
Soft seat set		H1

Specify if reduced trim.

How to order spares



Always order spares by using the description given in the column headed 'Available spares', and state the size and type of valve including the full product description of the product.

Example:

1 - PTFE stem seal kit for a Spirax Sarco Spira-trol™ DN25 LE43PTSUSS.2 Ky 10 two-port control valve.

How to fit spares

Full fitting instructions are given in the Installation and Maintenance Instructions supplied with the spare.



Spare parts

Spira-trol™ - L series with bellows seal

The spare parts available are shown in solid outline. Parts drawn in a grey line are not supplied as spares.

Note: When placing an order for spare parts please specify clearly the full product description as found on the label of the valve body, as this will ensure that the correct spare parts are supplied.

Available spares

Actuator clamping nut		A
Gasket set	(Non-bellows sealed)	B, G
Stem seal kit	Graphite packing and gasket set	C2
Plug stem and seat kit (No gaskets supplied)		D, E
Bellows seal assembly		F
PTFE or PEEK soft seat seal		H
Soft seat set		H1

Specify if reduced trim.

How to order spares


Always order spares by using the description given in the column headed 'Available spares', and state the size and type of valve including the full product description of the product.

Example:

1 - Plug stem and seat kit for a Spirax Sarco Spira-trol™ DN25 LE43PTSUSS.2 K_v 10 two-port control valve.

How to fit spares

Full fitting instructions are given in the Installation and Maintenance Instructions supplied with the spare.



Spira-trol™ selection guide:

Valve size	EN standard = DN15, DN20, DN25, DN32, DN40, DN50, DN65, DN80 and DN100 ASME standard = ½", ¾", 1", 1¼", 1½", 2", 2½", 3" and 4"	DN25
Valve series	L = L series 2-port control valve	L
Valve characteristic	E = Equal percentage F = Fast opening L = Linear	E
Flange type	A = ASME Blank = EN (PN)	Blank
Flow	Blank = under T = over	Blank
Material	3 = Cast iron 4 = Carbon steel 6 = Stainless steel	4
Connections	1 = Screwed 3 = Flanged	3
Stem sealing	P = PTFE H = Graphite N = PTFE/Nitronic bush (DN15 to DN50 only) D = Bellows V = PTFE for vacuum	P
Seating	T = 431 stainless steel G = PTFE soft seat S = 316L stainless steel W = 316L with stellite 6 facing P = Full PEEK K = PEEK soft seat	T
Type of trim	S = Standard trim A1 = 1 stage anticavitation A2 = 2 stage anticavitation P1 = 1 stage low noise cage P2 = 2 stage low noise cage P3 = 3 stage low noise cage	S
Trim balancing	U = Unbalanced B = Balanced (only available LEA series)	U
Bonnet type	S = Standard E = Extended	S
Bolting	S = Standard bolting H = High temperature (only available LE series)	S
Finish	Blank = Standard finish N = Nickel plated	Blank
Series	2 = .2	0.2
Kvs	To be specified	Kv 10
Connection type	To be specified	Flanged PN16

Selection example:

DN25	-	L	E	4	3	P	T	S	U	S	S	.2	-	Kv 10	-	Flanged PN16
------	---	---	---	---	---	---	---	---	---	---	---	----	---	-------	---	--------------

How to order

Example: 1 off Spirax Sarco Spira-trol™ DN25 LE43PTSUSS.2 Kv 10 two-port control valve having flanged PN16 connections.